

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261979

Luminaire Tested: P3AS05R459727DE010 E3DL1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1261979  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R459727DE010 E3DL1LI  
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 469.0 lumens  
Efficiency: N/A  
Efficacy: 65.1 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261979  
CATALOG NUMBER: P3AS05R459727DE010 E3DL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1261979  
 CATALOG NUMBER: P3AS05R459727DE010 E3DL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88				88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83				83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78				78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74				74
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70				70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66				66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62				62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59				59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57				57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	176126
5°	172000
10°	158113
15°	133962
20°	103936
25°	72657
30°	45779
35°	26957
40°	15257
45°	7412
50°	2559
55°	2103
60°	2017
65°	1972
70°	1859
75°	1779
80°	1642
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7412 cd/sqm



TEST NUMBER: P1261979  
 CATALOG NUMBER: P3AS05R459727DE010 E3DL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.3	15.4
10°-20°	162.0	34.6
20°-30°	137.6	29.3
30°-40°	65.7	14.0
40°-50°	19.8	4.2
50°-60°	5.0	1.1
60°-70°	3.7	0.8
70°-80°	2.2	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.0	79.3
0°-40°	437.6	93.3
0°-60°	462.4	98.6
0°-90°	469.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	469.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	803	
5°	781	72
15°	590	162
25°	300	138
35°	101	66
45°	24	20
55°	6	5
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1261979  
CATALOG NUMBER: P3AS05R459727DE010 E3DL1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	803.2
2.5°	798.2
5°	781.4
7.5°	752.4
10°	710.1
12.5°	653.9
15°	590.1
17.5°	519.2
20°	445.4
22.5°	370.4
25°	300.3
27.5°	236.6
30°	180.8
32.5°	135.9
35°	100.7
37.5°	74.2
40°	53.3
42.5°	36.9
45°	23.9
47.5°	13.4
50°	7.5
52.5°	5.9
55°	5.5
57.5°	5.0
60°	4.6
62.5°	4.2
65°	3.8
67.5°	3.4
70°	2.9
72.5°	2.5
75°	2.1
77.5°	1.7
80°	1.3
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)