

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247220

Luminaire Tested: P3AS17R209024DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247220
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209024DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1175.0 lumens
Efficiency: N/A
Efficacy: 55.4 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247220
CATALOG NUMBER: P3AS17R209024DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1247220

CATALOG NUMBER: P3AS17R209024DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	904028
5°	821790
10°	607359
15°	375712
20°	214545
25°	122499
30°	68694
35°	37370
40°	20467
45°	11257
50°	6584
55°	4779
60°	4473
65°	4099
70°	3654
75°	3813
80°	2904
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11257 cd/sqm



TEST NUMBER: P1247220
 CATALOG NUMBER: P3AS17R209024DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	323.3	27.5
10°-20°	461.5	39.3
20°-30°	240.9	20.5
30°-40°	93.1	7.9
40°-50°	30.2	2.6
50°-60°	11.9	1.0
60°-70°	7.9	0.7
70°-80°	4.6	0.4
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1025.7	87.3
0°-40°	1118.8	95.2
0°-60°	1161.0	98.8
0°-90°	1175.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1175.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4123	
5°	3733	323
15°	1655	462
25°	506	241
35°	140	93
45°	36	30
55°	12	12
65°	8	8
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P1247220
CATALOG NUMBER: P3AS17R209024DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4122.7
1°	4114.8
2°	4065.9
3°	3991.0
4°	3875.2
5°	3733.4
6°	3565.4
7°	3379.2
8°	3163.5
9°	2953.5
10°	2727.7
12.5°	2168.0
15°	1655.0
17.5°	1238.4
20°	919.4
22.5°	681.1
25°	506.3
27.5°	373.4
30°	271.3
32.5°	196.4
35°	139.6
37.5°	101.0
40°	71.5
42.5°	51.1
45°	36.3
47.5°	26.1
50°	19.3
52.5°	14.8
55°	12.5
57.5°	11.4
60°	10.2
62.5°	9.1
65°	7.9
67.5°	6.8
70°	5.7
72.5°	5.7
75°	4.5
77.5°	3.4
80°	2.3
82.5°	2.3
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)