

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262011

Luminaire Tested: P3AS05R509727DE010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262011  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R509727DE010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 472.0 lumens  
Efficiency: N/A  
Efficacy: 65.6 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262011  
CATALOG NUMBER: P3AS05R509727DE010 E3DL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1262011  
 CATALOG NUMBER: P3AS05R509727DE010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82	82	82	82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76	76	76	76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67	67	67	67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64	64	64	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57	57	57	57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54	54	54	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	150273
5°	147237
10°	137918
15°	123474
20°	103912
25°	79311
30°	51527
35°	30544
40°	17662
45°	8838
50°	3309
55°	2561
60°	2412
65°	2179
70°	2180
75°	2118
80°	2147
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8838 cd/sqm



TEST NUMBER: P1262011  
 CATALOG NUMBER: P3AS05R509727DE010 E3DL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.2	13.2
10°-20°	150.4	31.9
20°-30°	147.6	31.3
30°-40°	74.3	15.8
40°-50°	23.5	5.0
50°-60°	6.1	1.3
60°-70°	4.3	0.9
70°-80°	2.7	0.6
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.2	76.3
0°-40°	434.5	92.1
0°-60°	464.1	98.3
0°-90°	472.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	472.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	685	
5°	669	62
15°	544	150
25°	328	148
35°	114	74
45°	28	23
55°	7	6
65°	4	4
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1262011  
CATALOG NUMBER: P3AS05R509727DE010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	685.3
2.5°	681.1
5°	668.9
7.5°	647.1
10°	619.4
12.5°	583.8
15°	543.9
17.5°	497.7
20°	445.3
22.5°	388.6
25°	327.8
27.5°	263.1
30°	203.5
32.5°	153.2
35°	114.1
37.5°	84.4
40°	61.7
42.5°	43.6
45°	28.5
47.5°	16.4
50°	9.7
52.5°	7.1
55°	6.7
57.5°	5.9
60°	5.5
62.5°	5.0
65°	4.2
67.5°	3.8
70°	3.4
72.5°	2.9
75°	2.5
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)