

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247487

Luminaire Tested: P3AS17R709024DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247487
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709024DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1421.0 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247487

CATALOG NUMBER: P3AS17R709024DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1247487

CATALOG NUMBER: P3AS17R709024DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	282170
5°	269249
10°	256174
15°	249332
20°	240121
25°	227263
30°	211374
35°	177560
40°	114443
45°	53184
50°	13953
55°	3479
60°	3508
65°	2958
70°	2885
75°	2881
80°	2904
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 53184 cd/sqm

TEST NUMBER: P1247487

CATALOG NUMBER: P3AS17R709024DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.5	8.1
10°-20°	308.6	21.7
20°-30°	431.2	30.3
30°-40°	399.8	28.1
40°-50°	143.3	10.1
50°-60°	12.2	0.9
60°-70°	6.0	0.4
70°-80°	3.9	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	854.3	60.1
0°-40°	1254.1	88.3
0°-60°	1409.6	99.2
0°-90°	1421.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1421.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1287	
5°	1223	115
15°	1098	309
25°	939	431
35°	663	400
45°	172	143
55°	9	12
65°	6	6
75°	3	4
85°	1	2
90°	0	

TEST NUMBER: P1247487

CATALOG NUMBER: P3AS17R709024DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1286.8
2.5°	1267.5
5°	1223.2
7.5°	1182.3
10°	1150.5
12.5°	1124.4
15°	1098.3
17.5°	1066.5
20°	1029.0
22.5°	985.8
25°	939.3
27.5°	891.6
30°	834.8
32.5°	762.1
35°	663.3
37.5°	537.2
40°	399.8
42.5°	272.6
45°	171.5
47.5°	95.4
50°	40.9
52.5°	13.6
55°	9.1
57.5°	8.0
60°	8.0
62.5°	6.8
65°	5.7
67.5°	5.7
70°	4.5
72.5°	4.5
75°	3.4
77.5°	3.4
80°	2.3
82.5°	2.3
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)