

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262016

Luminaire Tested: P3AS05R509727DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262016
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509727DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 367.0 lumens
Efficiency: N/A
Efficacy: 51.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262016
CATALOG NUMBER: P3AS05R509727DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1262016
 CATALOG NUMBER: P3AS05R509727DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74577
5°	73475
10°	70228
15°	65040
20°	58455
25°	51390
30°	43703
35°	35442
40°	26621
45°	17149
50°	8153
55°	6423
60°	6052
65°	5656
70°	5129
75°	4575
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17149 cd/sqm



TEST NUMBER: P1262016
 CATALOG NUMBER: P3AS05R509727DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.3	8.5
10°-20°	79.9	21.8
20°-30°	97.1	26.4
30°-40°	82.3	22.4
40°-50°	42.8	11.7
50°-60°	15.4	4.2
60°-70°	10.7	2.9
70°-80°	5.8	1.6
80°-90°	1.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	208.2	56.7
0°-40°	290.6	79.2
0°-60°	348.7	95.0
0°-90°	367.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	367.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	340	
5°	334	31
15°	286	80
25°	212	97
35°	132	82
45°	55	43
55°	17	15
65°	11	11
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1262016
CATALOG NUMBER: P3AS05R509727DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	340.1
2.5°	338.9
5°	333.8
7.5°	326.3
10°	315.4
12.5°	301.6
15°	286.5
17.5°	269.3
20°	250.5
22.5°	231.2
25°	212.4
27.5°	192.7
30°	172.6
32.5°	152.5
35°	132.4
37.5°	112.7
40°	93.0
42.5°	74.1
45°	55.3
47.5°	36.9
50°	23.9
52.5°	18.4
55°	16.8
57.5°	15.1
60°	13.8
62.5°	12.1
65°	10.9
67.5°	9.2
70°	8.0
72.5°	6.7
75°	5.4
77.5°	4.2
80°	3.4
82.5°	2.5
85°	1.7
87.5°	0.8
90°	0.0

(END OF REPORT)