

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247514

Luminaire Tested: P3AS20R159024D010 E3CD1MB

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1247514  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R159024D010 E3CD1MB  
Description: 3in Adjustable LED luminaire with, R15 optic, 2400K CCT AND, 90CRI , E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1886.0 lumens  
Efficiency: N/A  
Efficacy: 65.5 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247514  
CATALOG NUMBER: P3AS20R159024D010 E3CD1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1247514  
 CATALOG NUMBER: P3AS20R159024D010 E3CD1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98	98	98
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	94	94	94
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	92	92	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	91	91	91
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	89	89	89
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	88	88	88
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	86	86	86
9	97	92	89	87	97	92	89	86	91	88	86	90	88	86	90	87	86	85	85	85
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	84	84	84

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3665934
5°	3072411
10°	1447223
15°	436325
20°	161457
25°	62762
30°	23396
35°	7174
40°	2548
45°	1395
50°	1023
55°	1147
60°	1316
65°	778
70°	962
75°	1271
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1395 cd/sqm



TEST NUMBER: P1247514  
 CATALOG NUMBER: P3AS20R159024D010 E3CD1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1079.1	57.2
10°-20°	641.4	34.0
20°-30°	134.7	7.1
30°-40°	21.7	1.2
40°-50°	3.7	0.2
50°-60°	2.7	0.1
60°-70°	1.7	0.1
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1855.3	98.4
0°-40°	1877.0	99.5
0°-60°	1883.4	99.9
0°-90°	1886.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1886.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	16718	
5°	13958	###
15°	1922	641
25°	259	135
35°	27	22
45°	4	4
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1247514  
CATALOG NUMBER: P3AS20R159024D010 E3CD1MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	16718.0
1°	16665.8
2°	16400.4
3°	15869.6
4°	15091.2
5°	13958.0
6°	12626.5
7°	11104.1
8°	9650.3
9°	8004.1
10°	6499.6
12.5°	3507.0
15°	1922.0
17.5°	1125.8
20°	691.9
22.5°	423.5
25°	259.4
27.5°	156.6
30°	92.4
32.5°	52.2
35°	26.8
37.5°	14.9
40°	8.9
42.5°	6.0
45°	4.5
47.5°	3.0
50°	3.0
52.5°	3.0
55°	3.0
57.5°	3.0
60°	3.0
62.5°	1.5
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)