

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262027

Luminaire Tested: P3AS05R559727DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559727DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 97CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 558.0 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262027

CATALOG NUMBER: P3AS05R559727DE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1262027

CATALOG NUMBER: P3AS05R559727DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	107		112	109	107	105		105	104	102		101	100	99		98	97	96
2	109	104	101	98		107	103	99	96		100	97	94		97	94	92		94	92	90
3	104	98	94	90		102	97	93	89		94	91	88		92	89	86		90	87	85
4	99	92	87	84		98	91	87	83		89	85	82		87	84	81		86	83	80
5	95	87	82	78		93	86	81	78		85	80	77		83	79	76		82	78	76
6	91	83	77	73		89	82	77	73		80	76	72		79	75	72		78	74	72
7	87	78	73	69		85	78	72	69		76	72	68		75	71	68		74	70	68
8	83	74	69	65		82	74	69	65		73	68	65		72	67	64		71	67	64
9	79	71	65	61		78	70	65	61		69	64	61		68	64	61		68	64	61
10	76	67	62	58		75	67	62	58		66	61	58		65	61	58		65	61	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	154768
5°	153334
10°	159494
15°	157277
20°	145029
25°	117999
30°	71682
35°	24815
40°	7070
45°	3380
50°	1433
55°	650
60°	746
65°	675
70°	513
75°	678
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3380 cd/sqm

TEST NUMBER: P1262027

CATALOG NUMBER: P3AS05R559727DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.3	12.1
10°-20°	192.5	34.5
20°-30°	214.7	38.5
30°-40°	70.2	12.6
40°-50°	9.2	1.7
50°-60°	2.0	0.4
60°-70°	1.1	0.2
70°-80°	0.7	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	474.5	85.0
0°-40°	544.8	97.6
0°-60°	556.0	99.6
0°-90°	558.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	558.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	706	
5°	697	67
15°	693	193
25°	488	215
35°	93	70
45°	11	9
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1262027

CATALOG NUMBER: P3AS05R559727DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	705.8
2.5°	700.7
5°	696.6
7.5°	706.6
10°	716.3
12.5°	711.2
15°	692.8
17.5°	663.4
20°	621.5
22.5°	563.6
25°	487.7
27.5°	391.3
30°	283.1
32.5°	173.6
35°	92.7
37.5°	47.0
40°	24.7
42.5°	15.9
45°	10.9
47.5°	7.5
50°	4.2
52.5°	2.5
55°	1.7
57.5°	1.7
60°	1.7
62.5°	1.3
65°	1.3
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)