

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247534

Luminaire Tested: P3AS20R159024D010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1247534  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R159024D010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R15 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 450.0 lumens  
Efficiency: N/A  
Efficacy: 15.6 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247534  
CATALOG NUMBER: P3AS20R159024D010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1247534  
 CATALOG NUMBER: P3AS20R159024D010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	97	96	95	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	92	90	88	86
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	87	84	82	80
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	82	79	77	75
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	78	75	72	70
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	74	71	68	66
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	71	67	64	62
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	68	63	60	59
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59	64	60	57	56
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	62	57	54	53
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	194041
5°	179352
10°	143195
15°	108150
20°	82374
25°	62762
30°	44969
35°	29339
40°	17977
45°	10885
50°	7232
55°	5582
60°	4824
65°	4151
70°	3719
75°	3728
80°	2778
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10885 cd/sqm



TEST NUMBER: P1247534  
 CATALOG NUMBER: P3AS20R159024D010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.2	16.0
10°-20°	133.2	29.6
20°-30°	118.6	26.3
30°-40°	70.1	15.6
40°-50°	28.8	6.4
50°-60°	13.5	3.0
60°-70°	8.2	1.8
70°-80°	4.3	1.0
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	323.9	72.0
0°-40°	394.0	87.6
0°-60°	436.3	97.0
0°-90°	450.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	450.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	885	
5°	815	72
15°	476	133
25°	259	119
35°	110	70
45°	35	29
55°	15	14
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1247534  
CATALOG NUMBER: P3AS20R159024D010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	884.9
1°	882.7
2°	876.2
3°	863.0
4°	841.1
5°	814.8
6°	786.3
7°	752.7
8°	717.6
9°	681.8
10°	643.1
12.5°	554.6
15°	476.4
17.5°	409.2
20°	353.0
22.5°	303.3
25°	259.4
27.5°	217.0
30°	177.6
32.5°	141.8
35°	109.6
37.5°	84.0
40°	62.8
42.5°	46.8
45°	35.1
47.5°	27.0
50°	21.2
52.5°	17.5
55°	14.6
57.5°	12.4
60°	11.0
62.5°	9.5
65°	8.0
67.5°	7.3
70°	5.8
72.5°	5.1
75°	4.4
77.5°	2.9
80°	2.2
82.5°	1.5
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)