

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262041

Luminaire Tested: P3AS05R559727DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262041  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R559727DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 97CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 174.0 lumens  
Efficiency: N/A  
Efficacy: 24.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262041  
CATALOG NUMBER: P3AS05R559727DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1262041  
 CATALOG NUMBER: P3AS05R559727DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	96	95	94	93	91			
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	32717
5°	32291
10°	31017
15°	29013
20°	26462
25°	23614
30°	20661
35°	17159
40°	13540
45°	9179
50°	5595
55°	2906
60°	2719
65°	2542
70°	2372
75°	2118
80°	2020
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9179 cd/sqm



TEST NUMBER: P1262041  
 CATALOG NUMBER: P3AS05R559727DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	13.8	7.9
10°-20°	35.7	20.5
20°-30°	44.7	25.7
30°-40°	39.9	23.0
40°-50°	23.4	13.4
50°-60°	8.1	4.6
60°-70°	4.9	2.8
70°-80°	2.7	1.6
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	94.2	54.2
0°-40°	134.2	77.1
0°-60°	165.6	95.2
0°-90°	174.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	174.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	149	
5°	147	14
15°	128	36
25°	98	45
35°	64	40
45°	30	23
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1262041  
CATALOG NUMBER: P3AS05R559727DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	149.2
2.5°	148.4
5°	146.7
7.5°	143.4
10°	139.3
12.5°	134.2
15°	127.8
17.5°	121.0
20°	113.4
22.5°	105.6
25°	97.6
27.5°	89.6
30°	81.6
32.5°	73.0
35°	64.1
37.5°	55.5
40°	47.3
42.5°	38.4
45°	29.6
47.5°	22.6
50°	16.4
52.5°	10.7
55°	7.6
57.5°	6.8
60°	6.2
62.5°	5.5
65°	4.9
67.5°	4.3
70°	3.7
72.5°	3.1
75°	2.5
77.5°	2.1
80°	1.6
82.5°	1.0
85°	0.6
87.5°	0.4
90°	0.0

(END OF REPORT)