

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262086

Luminaire Tested: P3AS05R659727DE010 E3CD1MMS

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262086  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R659727DE010 E3CD1MMS  
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 97CRI , E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 518.0 lumens  
Efficiency: N/A  
Efficacy: 71.9 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262086  
CATALOG NUMBER: P3AS05R659727DE010 E3CD1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1262086  
 CATALOG NUMBER: P3AS05R659727DE010 E3CD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87				87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81				81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75				75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70				70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66				66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62				62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58				58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54				54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51				51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	126591
5°	119150
10°	117633
15°	115551
20°	109093
25°	101256
30°	78696
35°	45534
40°	18349
45°	8435
50°	3275
55°	1300
60°	1096
65°	1090
70°	1090
75°	1101
80°	1010
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8435 cd/sqm



TEST NUMBER: P1262086  
 CATALOG NUMBER: P3AS05R659727DE010 E3CD1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.5	9.9
10°-20°	142.1	27.4
20°-30°	186.1	35.9
30°-40°	107.8	20.8
40°-50°	23.1	4.5
50°-60°	3.8	0.7
60°-70°	2.1	0.4
70°-80°	1.2	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.7	73.3
0°-40°	487.4	94.1
0°-60°	514.2	99.3
0°-90°	518.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	518.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	577	
5°	541	51
15°	509	142
25°	418	186
35°	170	108
45°	27	23
55°	3	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1262086  
CATALOG NUMBER: P3AS05R659727DE010 E3CD1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	577.3
2.5°	560.9
5°	541.3
7.5°	533.3
10°	528.3
12.5°	521.1
15°	509.0
17.5°	490.1
20°	467.5
22.5°	446.2
25°	418.5
27.5°	372.0
30°	310.8
32.5°	240.9
35°	170.1
37.5°	107.7
40°	64.1
42.5°	40.2
45°	27.2
47.5°	17.6
50°	9.6
52.5°	4.6
55°	3.4
57.5°	2.9
60°	2.5
62.5°	2.5
65°	2.1
67.5°	1.7
70°	1.7
72.5°	1.3
75°	1.3
77.5°	0.8
80°	0.8
82.5°	0.4
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)