

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247694

Luminaire Tested: P3AS20R459024D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247694
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459024D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R45 optic, 2400K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1999.1 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247694
CATALOG NUMBER: P3AS20R459024D010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1247694

CATALOG NUMBER: P3AS20R459024D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94	92	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	92	90	88	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	86	92	90	88	86
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	88	86	84	82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	85	82	80	79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	82	79	76	75
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	79	76	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	866685
5°	871294
10°	844518
15°	707723
20°	540984
25°	329342
30°	137034
35°	43902
40°	13654
45°	2760
50°	2047
55°	2294
60°	1974
65°	2335
70°	1923
75°	2542
80°	1894
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2760 cd/sqm



TEST NUMBER: P1247694
 CATALOG NUMBER: P3AS20R459024D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	373.3	18.7
10°-20°	856.8	42.9
20°-30°	616.9	30.9
30°-40°	128.3	6.4
40°-50°	11.7	0.6
50°-60°	4.9	0.2
60°-70°	3.9	0.2
70°-80°	2.6	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1847.1	92.4
0°-40°	1975.4	98.8
0°-60°	1992.0	99.6
0°-90°	1999.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1999.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3952	
5°	3958	373
15°	3118	857
25°	1361	617
35°	164	128
45°	9	12
55°	6	5
65°	4	4
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P1247694
CATALOG NUMBER: P3AS20R459024D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3952.4
2.5°	3953.8
5°	3958.3
7.5°	3930.0
10°	3792.8
12.5°	3506.6
15°	3117.5
17.5°	2719.4
20°	2318.3
22.5°	1857.7
25°	1361.2
27.5°	897.5
30°	541.2
32.5°	302.7
35°	164.0
37.5°	92.4
40°	47.7
42.5°	20.9
45°	8.9
47.5°	6.0
50°	6.0
52.5°	6.0
55°	6.0
57.5°	4.5
60°	4.5
62.5°	4.5
65°	4.5
67.5°	3.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)