

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262092

Luminaire Tested: P3AS05R659727DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262092
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659727DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 500.0 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262092

CATALOG NUMBER: P3AS05R659727DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1262092

CATALOG NUMBER: P3AS05R659727DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	102		101	100	99		98	97	96
2	108	104	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	95	91	88		93	89	86		90	87	85		88	86	83
4	98	91	85	81		96	90	85	81		87	83	80		85	82	79		84	81	78
5	93	85	79	75		92	84	79	75		82	78	74		81	77	74		79	76	73
6	89	80	74	70		87	79	74	70		78	73	69		76	72	69		75	71	68
7	84	75	70	65		83	75	69	65		73	69	65		72	68	65		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		68	63	60
9	77	67	61	58		76	67	61	57		66	61	57		65	60	57		64	60	57
10	73	64	58	54		72	63	58	54		62	57	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133980
5°	124411
10°	120305
15°	115937
20°	107179
25°	97651
30°	75455
35°	43741
40°	17347
45°	7381
50°	1740
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7381 cd/sqm

TEST NUMBER: P1262092

CATALOG NUMBER: P3AS05R659727DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.3	10.7
10°-20°	142.3	28.5
20°-30°	180.1	36.0
30°-40°	102.6	20.5
40°-50°	20.4	4.1
50°-60°	1.0	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	375.7	75.1
0°-40°	478.3	95.7
0°-60°	499.7	99.9
0°-90°	500.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	500.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	611	
5°	565	53
15°	511	142
25°	404	180
35°	163	103
45°	24	20
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1262092

CATALOG NUMBER: P3AS05R659727DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	611.0
1°	606.5
2°	596.6
3°	585.1
4°	573.8
5°	565.2
6°	558.8
7°	553.7
8°	549.1
9°	544.6
10°	540.3
11°	535.6
12°	530.6
13°	524.7
14°	518.3
15°	510.7
16°	501.7
17°	491.8
18°	481.1
19°	469.8
20°	459.3
21°	448.6
22°	439.0
23°	428.9
24°	417.2
25°	403.6
26°	387.4
27°	367.9
28°	345.9
29°	322.4
30°	298.0
31°	271.1
32°	244.4
32.5°	230.6
33°	217.2
34°	190.1
35°	163.4
36°	138.7
37°	114.3
37.5°	101.7
38°	91.7
39°	74.2
40°	60.6
42.5°	37.4
45°	23.8



TEST NUMBER: P1262092

CATALOG NUMBER: P3AS05R659727DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	14.0
50°	5.1
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)