

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247821

Luminaire Tested: P3AS20R659024D010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247821
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659024D010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1174.0 lumens
Efficiency: N/A
Efficacy: 40.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247821
CATALOG NUMBER: P3AS20R659024D010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1247821
 CATALOG NUMBER: P3AS20R659024D010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	208909
5°	206097
10°	199195
15°	187856
20°	173265
25°	157291
30°	139313
35°	118534
40°	94320
45°	66581
50°	38651
55°	21103
60°	19604
65°	17797
70°	16221
75°	15166
80°	13133
85°	11322

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 66581 cd/sqm



TEST NUMBER: P1247821
 CATALOG NUMBER: P3AS20R659024D010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.1	7.5
10°-20°	231.5	19.7
20°-30°	297.5	25.3
30°-40°	275.2	23.4
40°-50°	166.1	14.2
50°-60°	56.7	4.8
60°-70°	34.1	2.9
70°-80°	19.3	1.6
80°-90°	5.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	617.1	52.6
0°-40°	892.3	76.0
0°-60°	1115.2	95.0
0°-90°	1174.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1174.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	953	
5°	936	88
15°	828	232
25°	650	298
35°	443	275
45°	215	166
55°	55	57
65°	34	34
75°	18	19
85°	4	5
90°	0	



TEST NUMBER: P1247821
CATALOG NUMBER: P3AS20R659024D010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	952.7
2.5°	948.3
5°	936.3
7.5°	918.5
10°	894.6
12.5°	864.8
15°	827.5
17.5°	787.2
20°	742.5
22.5°	696.3
25°	650.1
27.5°	600.9
30°	550.2
32.5°	499.5
35°	442.8
37.5°	387.7
40°	329.5
42.5°	271.4
45°	214.7
47.5°	162.5
50°	113.3
52.5°	71.6
55°	55.2
57.5°	49.2
60°	44.7
62.5°	38.8
65°	34.3
67.5°	29.8
70°	25.3
72.5°	22.4
75°	17.9
77.5°	14.9
80°	10.4
82.5°	7.5
85°	4.5
87.5°	3.0
90°	0.0

(END OF REPORT)