

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262109

Luminaire Tested: P3AS05R659727DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262109
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659727DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 420.0 lumens
Efficiency: N/A
Efficacy: 58.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262109

CATALOG NUMBER: P3AS05R659727DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1262109

CATALOG NUMBER: P3AS05R659727DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63		
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99049
5°	97865
10°	94142
15°	88196
20°	79317
25°	67359
30°	52692
35°	37530
40°	24560
45°	15195
50°	7710
55°	2714
60°	2368
65°	2387
70°	2116
75°	2118
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 15195 cd/sqm

TEST NUMBER: P1262109

CATALOG NUMBER: P3AS05R659727DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.7	9.9
10°-20°	108.1	25.7
20°-30°	126.4	30.1
30°-40°	88.3	21.0
40°-50°	38.9	9.3
50°-60°	8.6	2.1
60°-70°	4.4	1.0
70°-80°	2.6	0.6
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	276.2	65.8
0°-40°	364.5	86.8
0°-60°	412.0	98.1
0°-90°	420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	420.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	452	
5°	445	42
15°	388	108
25°	278	126
35°	140	88
45°	49	39
55°	7	9
65°	5	4
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1262109

CATALOG NUMBER: P3AS05R659727DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	451.7
2.5°	450.0
5°	444.6
7.5°	435.4
10°	422.8
12.5°	407.3
15°	388.5
17.5°	365.5
20°	339.9
22.5°	311.0
25°	278.4
27.5°	244.1
30°	208.1
32.5°	173.3
35°	140.2
37.5°	111.4
40°	85.8
42.5°	64.9
45°	49.0
47.5°	36.0
50°	22.6
52.5°	11.7
55°	7.1
57.5°	6.3
60°	5.4
62.5°	5.0
65°	4.6
67.5°	3.8
70°	3.3
72.5°	2.9
75°	2.5
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)