

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262117

Luminaire Tested: P3AS05R709727DE010 E3D1H

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262117  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R709727DE010 E3D1H  
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 500.0 lumens  
Efficiency: N/A  
Efficacy: 69.4 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262117  
CATALOG NUMBER: P3AS05R709727DE010 E3D1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1262117  
 CATALOG NUMBER: P3AS05R709727DE010 E3D1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	97229
5°	91679
10°	86928
15°	85358
20°	82280
25°	77569
30°	76999
35°	67057
40°	43396
45°	20498
50°	2866
55°	229
60°	175
65°	208
70°	128
75°	169
80°	253
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20498 cd/sqm



TEST NUMBER: P1262117  
 CATALOG NUMBER: P3AS05R709727DE010 E3D1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.9	7.8
10°-20°	105.6	21.1
20°-30°	149.4	29.9
30°-40°	150.1	30.0
40°-50°	54.0	10.8
50°-60°	1.4	0.3
60°-70°	0.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.9	58.8
0°-40°	444.0	88.8
0°-60°	499.4	99.9
0°-90°	500.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	500.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	443	
5°	416	39
15°	376	106
25°	321	149
35°	250	150
45°	66	54
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1262117  
CATALOG NUMBER: P3AS05R709727DE010 E3D1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	443.4
1°	442.1
2°	438.2
3°	432.1
4°	424.3
5°	416.5
6°	409.1
7°	403.3
8°	398.2
9°	394.1
10°	390.4
11°	387.3
12°	384.4
13°	381.6
14°	378.9
15°	376.0
16°	372.5
17°	368.8
18°	364.3
19°	358.8
20°	352.6
21°	345.8
22°	339.0
23°	332.5
24°	326.1
25°	320.6
26°	316.7
27°	313.6
28°	311.1
29°	308.2
30°	304.1
31°	298.2
32°	289.8
32.5°	285.0
33°	278.7
34°	266.1
35°	250.5
36°	233.3
37°	213.8
37.5°	204.7
38°	192.4
39°	170.4
40°	151.6
42.5°	104.9
45°	66.1



TEST NUMBER: P1262117  
CATALOG NUMBER: P3AS05R709727DE010 E3D1H

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	35.5
50°	8.4
52.5°	1.0
55°	0.6
57.5°	0.6
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)