

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261337

Luminaire Tested: P3AS02R109727DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R109727DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R10 optic, 2700K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 148.0 lumens
Efficiency: N/A
Efficacy: 39.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261337

CATALOG NUMBER: P3AS02R109727DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1261337

CATALOG NUMBER: P3AS02R109727DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37322
5°	36320
10°	33199
15°	29081
20°	24946
25°	20832
30°	16661
35°	12501
40°	9074
45°	5923
50°	3718
55°	2523
60°	2237
65°	2024
70°	1923
75°	1779
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5923 cd/sqm

TEST NUMBER: P1261337

CATALOG NUMBER: P3AS02R109727DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.2	10.3
10°-20°	35.7	24.1
20°-30°	39.3	26.6
30°-40°	29.4	19.9
40°-50°	15.2	10.3
50°-60°	6.3	4.3
60°-70°	3.9	2.6
70°-80°	2.2	1.5
80°-90°	0.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	90.2	61.0
0°-40°	119.7	80.8
0°-60°	141.3	95.4
0°-90°	148.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	148.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	170	
5°	165	15
15°	128	36
25°	86	39
35°	47	29
45°	19	15
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1261337

CATALOG NUMBER: P3AS02R109727DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	170.2
1°	170.4
2°	169.9
3°	168.7
4°	167.1
5°	165.0
6°	162.4
7°	159.6
8°	156.2
9°	152.6
10°	149.1
12.5°	138.7
15°	128.1
17.5°	117.4
20°	106.9
22.5°	96.2
25°	86.1
27.5°	75.9
30°	65.8
32.5°	55.9
35°	46.7
37.5°	38.8
40°	31.7
42.5°	25.1
45°	19.1
47.5°	14.4
50°	10.9
52.5°	8.1
55°	6.6
57.5°	5.8
60°	5.1
62.5°	4.5
65°	3.9
67.5°	3.4
70°	3.0
72.5°	2.4
75°	2.1
77.5°	1.7
80°	1.3
82.5°	0.9
85°	0.6
87.5°	0.2
90°	0.0

(END OF REPORT)