

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262122

Luminaire Tested: P3AS05R709727DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262122
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709727DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 207.0 lumens
Efficiency: N/A
Efficacy: 28.8 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262122

CATALOG NUMBER: P3AS05R709727DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1262122

CATALOG NUMBER: P3AS05R709727DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40063
5°	39599
10°	38454
15°	36822
20°	34490
25°	31332
30°	27067
35°	21576
40°	15715
45°	10327
50°	4844
55°	1491
60°	1447
65°	1401
70°	1346
75°	1356
80°	1263
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10327 cd/sqm

TEST NUMBER: P1262122

CATALOG NUMBER: P3AS05R709727DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.9	8.2
10°-20°	45.4	21.9
20°-30°	59.0	28.5
30°-40°	50.1	24.2
40°-50°	25.8	12.5
50°-60°	5.0	2.4
60°-70°	2.7	1.3
70°-80°	1.6	0.8
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	121.3	58.6
0°-40°	171.4	82.8
0°-60°	202.2	97.7
0°-90°	207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	207.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	183	
5°	180	17
15°	162	45
25°	130	59
35°	81	50
45°	33	26
55°	4	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1262122

CATALOG NUMBER: P3AS05R709727DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	182.7
2.5°	182.1
5°	179.9
7.5°	176.6
10°	172.7
12.5°	167.7
15°	162.2
17.5°	155.4
20°	147.8
22.5°	139.2
25°	129.5
27.5°	118.6
30°	106.9
32.5°	93.9
35°	80.6
37.5°	67.4
40°	54.9
42.5°	43.2
45°	33.3
47.5°	24.5
50°	14.2
52.5°	6.2
55°	3.9
57.5°	3.7
60°	3.3
62.5°	3.1
65°	2.7
67.5°	2.5
70°	2.1
72.5°	1.9
75°	1.6
77.5°	1.2
80°	1.0
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)