

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262126

Luminaire Tested: P3AS05R709727DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709727DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 301.0 lumens
Efficiency: N/A
Efficacy: 41.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262126
CATALOG NUMBER: P3AS05R709727DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1262126
 CATALOG NUMBER: P3AS05R709727DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70608
5°	69315
10°	65352
15°	59319
20°	51875
25°	43769
30°	35828
35°	27786
40°	19894
45°	12590
50°	6277
55°	3823
60°	3289
65°	3061
70°	2693
75°	2457
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12590 cd/sqm



TEST NUMBER: P1262126
 CATALOG NUMBER: P3AS05R709727DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.4	9.8
10°-20°	72.7	24.2
20°-30°	82.8	27.5
30°-40°	64.7	21.5
40°-50°	31.8	10.6
50°-60°	9.8	3.2
60°-70°	5.8	1.9
70°-80°	3.1	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	184.9	61.4
0°-40°	249.6	82.9
0°-60°	291.2	96.7
0°-90°	301.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	301.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	322	
5°	315	29
15°	261	73
25°	181	83
35°	104	65
45°	41	32
55°	10	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1262126
CATALOG NUMBER: P3AS05R709727DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	322.0
2.5°	320.3
5°	314.9
7.5°	306.1
10°	293.5
12.5°	278.8
15°	261.3
17.5°	242.4
20°	222.3
22.5°	201.4
25°	180.9
27.5°	160.8
30°	141.5
32.5°	122.3
35°	103.8
37.5°	86.3
40°	69.5
42.5°	54.0
45°	40.6
47.5°	28.5
50°	18.4
52.5°	12.1
55°	10.0
57.5°	8.8
60°	7.5
62.5°	6.7
65°	5.9
67.5°	5.0
70°	4.2
72.5°	3.3
75°	2.9
77.5°	2.5
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)