

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262128

Luminaire Tested: P3AS05R709727DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709727DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 148.0 lumens
Efficiency: N/A
Efficacy: 20.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262128

CATALOG NUMBER: P3AS05R709727DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1262128

CATALOG NUMBER: P3AS05R709727DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34712
5°	34074
10°	32130
15°	29172
20°	25506
25°	21509
30°	17623
35°	13679
40°	9790
45°	6202
50°	3104
55°	1873
60°	1623
65°	1505
70°	1346
75°	1186
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6202 cd/sqm

TEST NUMBER: P1262128

CATALOG NUMBER: P3AS05R709727DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.4	9.8
10°-20°	35.7	24.2
20°-30°	40.7	27.5
30°-40°	31.8	21.5
40°-50°	15.7	10.6
50°-60°	4.8	3.2
60°-70°	2.9	1.9
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	90.9	61.4
0°-40°	122.7	82.9
0°-60°	143.2	96.8
0°-90°	148.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	148.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	158	
5°	155	14
15°	128	36
25°	89	41
35°	51	32
45°	20	16
55°	5	5
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1262128

CATALOG NUMBER: P3AS05R709727DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	158.3
2.5°	157.5
5°	154.8
7.5°	150.5
10°	144.3
12.5°	137.1
15°	128.5
17.5°	119.2
20°	109.3
22.5°	99.0
25°	88.9
27.5°	79.1
30°	69.6
32.5°	60.1
35°	51.1
37.5°	42.4
40°	34.2
42.5°	26.6
45°	20.0
47.5°	14.0
50°	9.1
52.5°	6.0
55°	4.9
57.5°	4.3
60°	3.7
62.5°	3.3
65°	2.9
67.5°	2.5
70°	2.1
72.5°	1.6
75°	1.4
77.5°	1.2
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)