

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261401

Luminaire Tested: P3AS02R159727DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261401
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159727DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 161.0 lumens
Efficiency: N/A
Efficacy: 44.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261401

CATALOG NUMBER: P3AS02R159727DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1261401

CATALOG NUMBER: P3AS02R159727DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	109	107	104		110	107	105	102		103	101	99		99	98	96		96	95	93
2	106	100	96	92		104	99	95	91		95	92	89		92	90	87		90	87	85
3	100	93	87	83		98	91	86	82		89	84	81		86	82	79		84	81	78
4	94	86	80	75		92	85	79	74		82	77	73		80	76	73		78	75	72
5	89	80	73	68		87	79	73	68		77	72	67		75	71	67		74	69	66
6	84	74	68	63		83	73	67	63		72	66	62		70	66	62		69	65	61
7	80	70	63	58		78	69	63	58		67	62	58		66	61	58		65	61	57
8	76	65	59	54		74	65	58	54		63	58	54		62	57	54		61	57	53
9	72	61	55	51		71	61	55	51		60	54	50		59	54	50		58	53	50
10	68	58	52	48		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40611
5°	39511
10°	36094
15°	31623
20°	27139
25°	22646
30°	18129
35°	13599
40°	9876
45°	6450
50°	4025
55°	2714
60°	2412
65°	2231
70°	2116
75°	1864
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6450 cd/sqm

TEST NUMBER: P1261401

CATALOG NUMBER: P3AS02R159727DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.6	10.3
10°-20°	38.8	24.1
20°-30°	42.8	26.6
30°-40°	32.0	19.9
40°-50°	16.6	10.3
50°-60°	6.9	4.3
60°-70°	4.3	2.7
70°-80°	2.4	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	98.1	61.0
0°-40°	130.2	80.9
0°-60°	153.6	95.4
0°-90°	161.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	161.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	185	
5°	180	17
15°	139	39
25°	94	43
35°	51	32
45°	21	17
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1261401

CATALOG NUMBER: P3AS02R159727DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	185.2
1°	185.4
2°	184.8
3°	183.6
4°	181.7
5°	179.5
6°	176.6
7°	173.6
8°	169.9
9°	166.0
10°	162.1
12.5°	150.9
15°	139.3
17.5°	127.7
20°	116.3
22.5°	104.6
25°	93.6
27.5°	82.6
30°	71.6
32.5°	60.8
35°	50.8
37.5°	42.2
40°	34.5
42.5°	27.3
45°	20.8
47.5°	15.7
50°	11.8
52.5°	8.8
55°	7.1
57.5°	6.3
60°	5.5
62.5°	4.9
65°	4.3
67.5°	3.7
70°	3.3
72.5°	2.7
75°	2.2
77.5°	1.8
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.2
90°	0.0

(END OF REPORT)