

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262233

Luminaire Tested: P3AS09R259727DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259727DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 828.0 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262233

CATALOG NUMBER: P3AS09R259727DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1262233

CATALOG NUMBER: P3AS09R259727DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	96	96
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	93	93
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	91	91
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	89	88	88
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	87	86	86
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	84	84
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	83	82	82
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	80	80
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	79	78	78
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	77	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	906813
5°	840037
10°	649955
15°	310444
20°	102349
25°	43140
30°	16711
35°	7228
40°	2405
45°	1116
50°	409
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1116 cd/sqm

TEST NUMBER: P1262233

CATALOG NUMBER: P3AS09R259727DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	335.4	40.5
10°-20°	381.5	46.1
20°-30°	88.7	10.7
30°-40°	18.6	2.2
40°-50°	3.0	0.4
50°-60°	0.5	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	805.6	97.3
0°-40°	824.2	99.5
0°-60°	827.7	100.0
0°-90°	828.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	828.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4135	
5°	3816	335
15°	1368	382
25°	178	89
35°	27	19
45°	4	3
55°	1	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1262233

CATALOG NUMBER: P3AS09R259727DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4135.4
1°	4127.0
2°	4084.1
3°	4023.7
4°	3931.6
5°	3816.3
6°	3668.3
7°	3513.4
8°	3339.5
9°	3143.5
10°	2919.0
11°	2658.7
12°	2360.0
13°	2032.7
14°	1690.5
15°	1367.5
16°	1081.7
17°	842.7
18°	662.9
19°	530.2
20°	438.6
21°	366.6
22°	307.7
23°	257.0
24°	215.0
25°	178.3
27.5°	105.7
30°	66.0
32.5°	42.3
35°	27.0
37.5°	16.2
40°	8.4
42.5°	5.4
45°	3.6
47.5°	2.1
50°	1.2
52.5°	0.6
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0



TEST NUMBER: P1262233

CATALOG NUMBER: P3AS09R259727DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)