

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262240

Luminaire Tested: P3AS09R259727DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259727DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 641.0 lumens
Efficiency: N/A
Efficacy: 57.7 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262240

CATALOG NUMBER: P3AS09R259727DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1262240

CATALOG NUMBER: P3AS09R259727DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	86	81	78		84	80	77		83	79	77		82	78	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	411173
5°	383622
10°	307320
15°	208605
20°	126221
25°	73819
30°	42032
35°	23129
40°	12280
45°	6450
50°	3753
55°	2829
60°	2412
65°	2542
70°	2372
75°	2118
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6450 cd/sqm

TEST NUMBER: P1262240

CATALOG NUMBER: P3AS09R259727DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.7	24.1
10°-20°	252.6	39.4
20°-30°	144.3	22.5
30°-40°	57.0	8.9
40°-50°	17.5	2.7
50°-60°	6.9	1.1
60°-70°	4.6	0.7
70°-80°	2.6	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	551.6	86.1
0°-40°	608.6	94.9
0°-60°	633.0	98.7
0°-90°	641.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	641.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1875	
5°	1743	155
15°	919	253
25°	305	144
35°	86	57
45°	21	17
55°	7	7
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1262240

CATALOG NUMBER: P3AS09R259727DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1875.1
1°	1871.4
2°	1856.1
3°	1829.2
4°	1791.8
5°	1742.8
6°	1685.2
7°	1620.3
8°	1544.9
9°	1467.8
10°	1380.2
11°	1293.8
12°	1198.8
13°	1105.1
14°	1008.9
15°	918.9
17.5°	712.4
20°	540.9
22.5°	406.1
25°	305.1
27.5°	226.0
30°	166.0
32.5°	120.1
35°	86.4
37.5°	61.3
40°	42.9
42.5°	29.4
45°	20.8
47.5°	14.7
50°	11.0
52.5°	8.6
55°	7.4
57.5°	6.7
60°	5.5
62.5°	4.9
65°	4.9
67.5°	4.3
70°	3.7
72.5°	3.1
75°	2.5
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.6



TEST NUMBER: P1262240
CATALOG NUMBER: P3AS09R259727DE010 E3DL1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)