

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261460

Luminaire Tested: P3AS02R259727DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261460
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259727DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 164.0 lumens
Efficiency: N/A
Efficacy: 45.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261460

CATALOG NUMBER: P3AS02R259727DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1261460

CATALOG NUMBER: P3AS02R259727DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38966
5°	38036
10°	35248
15°	31396
20°	26976
25°	22937
30°	18889
35°	14723
40°	10591
45°	6729
50°	3957
55°	2753
60°	2500
65°	2335
70°	2116
75°	1864
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6729 cd/sqm

TEST NUMBER: P1261460

CATALOG NUMBER: P3AS02R259727DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.0	9.8
10°-20°	38.4	23.4
20°-30°	43.4	26.5
30°-40°	34.3	20.9
40°-50°	17.3	10.6
50°-60°	6.9	4.2
60°-70°	4.5	2.7
70°-80°	2.4	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	97.8	59.6
0°-40°	132.2	80.6
0°-60°	156.4	95.4
0°-90°	164.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	164.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	178	
5°	173	16
15°	138	38
25°	95	43
35°	55	34
45°	22	17
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1261460

CATALOG NUMBER: P3AS02R259727DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	177.7
1°	177.7
2°	177.1
3°	176.1
4°	174.7
5°	172.8
6°	170.6
7°	167.9
8°	165.1
9°	161.8
10°	158.3
11°	154.5
12°	150.8
13°	146.5
14°	142.4
15°	138.3
17.5°	126.9
20°	115.6
22.5°	105.0
25°	94.8
27.5°	84.8
30°	74.6
32.5°	65.0
35°	55.0
37.5°	45.8
40°	37.0
42.5°	28.8
45°	21.7
47.5°	16.1
50°	11.6
52.5°	8.8
55°	7.2
57.5°	6.5
60°	5.7
62.5°	5.1
65°	4.5
67.5°	3.9
70°	3.3
72.5°	2.9
75°	2.2
77.5°	1.8
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.2



TEST NUMBER: P1261460

CATALOG NUMBER: P3AS02R259727DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)