

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262291

Luminaire Tested: P3AS09R359727DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359727DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 778.0 lumens
Efficiency: N/A
Efficacy: 70.1 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262291

CATALOG NUMBER: P3AS09R359727DE010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1262291

CATALOG NUMBER: P3AS09R359727DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		112	110	109	107		106	105	104		103	102	101		99	99	98
2	111	107	104	101		109	105	103	100		102	100	98		99	98	96		97	95	94
3	107	102	98	95		105	101	98	95		98	96	93		96	94	92		94	92	90
4	104	98	94	91		102	97	93	90		95	92	89		93	90	88		91	89	87
5	100	94	90	87		99	93	89	86		92	88	86		90	87	85		89	86	84
6	97	91	86	83		96	90	86	83		89	85	82		87	84	82		86	83	81
7	94	87	83	80		93	87	83	80		86	82	79		85	81	79		84	81	79
8	91	84	80	77		90	84	80	77		83	79	77		82	79	76		81	78	76
9	89	82	77	74		88	81	77	74		80	77	74		80	76	74		79	76	74
10	86	79	75	72		85	79	75	72		78	74	72		77	74	72		77	74	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	507306
5°	496983
10°	462338
15°	338958
20°	173568
25°	62568
30°	24358
35°	8539
40°	3521
45°	961
50°	853
55°	956
60°	789
65°	623
70°	769
75°	1017
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 75°
Luminance: 1017 cd/sqm

TEST NUMBER: P1262291

CATALOG NUMBER: P3AS09R359727DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.5	27.1
10°-20°	394.9	50.8
20°-30°	139.8	18.0
30°-40°	24.5	3.1
40°-50°	3.6	0.5
50°-60°	2.0	0.3
60°-70°	1.4	0.2
70°-80°	1.0	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	745.2	95.8
0°-40°	769.7	98.9
0°-60°	775.3	99.7
0°-90°	778.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	778.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2314	
5°	2258	210
15°	1493	395
25°	259	140
35°	32	24
45°	3	4
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1262291

CATALOG NUMBER: P3AS09R359727DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2313.5
1°	2312.9
2°	2305.5
3°	2291.5
4°	2278.6
5°	2257.8
6°	2236.3
7°	2212.4
8°	2183.0
9°	2137.1
10°	2076.4
11°	1992.5
12°	1891.4
13°	1771.3
14°	1638.9
15°	1493.1
17.5°	1112.0
20°	743.8
22.5°	448.5
25°	258.6
27.5°	154.4
30°	96.2
32.5°	55.8
35°	31.9
37.5°	20.2
40°	12.3
42.5°	6.1
45°	3.1
47.5°	2.5
50°	2.5
52.5°	2.5
55°	2.5
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.2
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0



TEST NUMBER: P1262291

CATALOG NUMBER: P3AS09R359727DE010 E3CB1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)