

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261481

Luminaire Tested: P3AS02R309727DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261481
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309727DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 106.0 lumens
Efficiency: N/A
Efficacy: 29.4 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261481

CATALOG NUMBER: P3AS02R309727DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1261481

CATALOG NUMBER: P3AS02R309727DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		79
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61859
5°	58882
10°	49520
15°	35710
20°	22145
25°	12606
30°	6988
35°	3801
40°	2004
45°	1085
50°	580
55°	382
60°	351
65°	363
70°	321
75°	254
80°	253
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1085 cd/sqm

TEST NUMBER: P1261481

CATALOG NUMBER: P3AS02R309727DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.1	22.7
10°-20°	42.8	40.4
20°-30°	24.7	23.4
30°-40°	9.4	8.8
40°-50°	2.9	2.7
50°-60°	1.0	0.9
60°-70°	0.7	0.6
70°-80°	0.4	0.3
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	91.6	86.5
0°-40°	101.0	95.3
0°-60°	104.9	98.9
0°-90°	106.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	106.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	282	
5°	268	24
15°	157	43
25°	52	25
35°	14	9
45°	4	3
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1261481

CATALOG NUMBER: P3AS02R309727DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	282.1
1°	281.9
2°	280.2
3°	277.0
4°	273.0
5°	267.5
6°	260.4
7°	252.6
8°	243.9
9°	233.5
10°	222.4
11°	210.4
12°	197.7
13°	184.3
14°	170.8
15°	157.3
17.5°	124.1
20°	94.9
22.5°	70.4
25°	52.1
27.5°	37.9
30°	27.6
32.5°	19.9
35°	14.2
37.5°	9.9
40°	7.0
42.5°	4.9
45°	3.5
47.5°	2.4
50°	1.7
52.5°	1.2
55°	1.0
57.5°	0.9
60°	0.8
62.5°	0.7
65°	0.7
67.5°	0.6
70°	0.5
72.5°	0.4
75°	0.3
77.5°	0.3
80°	0.2
82.5°	0.2
85°	0.1
87.5°	0.0



TEST NUMBER: P1261481
CATALOG NUMBER: P3AS02R309727DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)