

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262308

Luminaire Tested: P3AS09R359727DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359727DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 495.9 lumens
Efficiency: N/A
Efficacy: 44.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262308
CATALOG NUMBER: P3AS09R359727DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1262308
 CATALOG NUMBER: P3AS09R359727DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113302
5°	110896
10°	103850
15°	93235
20°	81090
25°	69101
30°	57882
35°	46097
40°	33348
45°	21087
50°	11496
55°	7952
60°	7543
65°	7005
70°	6668
75°	5676
80°	5430
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21087 cd/sqm



TEST NUMBER: P1262308
 CATALOG NUMBER: P3AS09R359727DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.9	9.5
10°-20°	114.3	23.0
20°-30°	131.0	26.4
30°-40°	106.9	21.5
40°-50°	53.9	10.9
50°-60°	20.0	4.0
60°-70°	13.4	2.7
70°-80°	7.4	1.5
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	292.1	58.9
0°-40°	399.0	80.5
0°-60°	472.9	95.3
0°-90°	495.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	495.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	517	
5°	504	47
15°	411	114
25°	286	131
35°	172	107
45°	68	54
55°	21	20
65°	14	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1262308
CATALOG NUMBER: P3AS09R359727DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	516.7
1°	516.1
2°	514.9
3°	512.4
4°	508.7
5°	503.8
6°	497.7
7°	491.6
8°	483.6
9°	475.6
10°	466.4
11°	456.6
12°	446.2
13°	434.6
14°	422.3
15°	410.7
17.5°	379.4
20°	347.5
22.5°	315.0
25°	285.6
27.5°	256.8
30°	228.6
32.5°	200.4
35°	172.2
37.5°	144.0
40°	116.5
42.5°	90.7
45°	68.0
47.5°	49.0
50°	33.7
52.5°	24.5
55°	20.8
57.5°	19.0
60°	17.2
62.5°	15.3
65°	13.5
67.5°	11.6
70°	10.4
72.5°	8.6
75°	6.7
77.5°	5.5
80°	4.3
82.5°	3.1
85°	1.8
87.5°	1.2



TEST NUMBER: P1262308
CATALOG NUMBER: P3AS09R359727DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)