

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262315

Luminaire Tested: P3AS09R359727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 397.0 lumens
Efficiency: N/A
Efficacy: 35.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262315

CATALOG NUMBER: P3AS09R359727DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1262315

CATALOG NUMBER: P3AS09R359727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127599
5°	124455
10°	113781
15°	96573
20°	76447
25°	57826
30°	42108
35°	28482
40°	17490
45°	10048
50°	6038
55°	4893
60°	4298
65°	3788
70°	3142
75°	3135
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 10048 cd/sqm

TEST NUMBER: P1262315

CATALOG NUMBER: P3AS09R359727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	13.2
10°-20°	117.3	29.5
20°-30°	109.7	27.6
30°-40°	67.2	16.9
40°-50°	26.5	6.7
50°-60°	11.7	2.9
60°-70°	7.3	1.8
70°-80°	3.9	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.3	70.3
0°-40°	346.4	87.3
0°-60°	384.5	96.9
0°-90°	397.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	397.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	582	
5°	565	52
15°	425	117
25°	239	110
35°	106	67
45°	32	26
55°	13	12
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1262315

CATALOG NUMBER: P3AS09R359727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	581.9
1°	582.5
2°	580.7
3°	577.0
4°	571.5
5°	565.4
6°	557.5
7°	548.3
8°	537.3
9°	525.1
10°	511.0
11°	496.4
12°	480.5
13°	463.3
14°	444.4
15°	425.4
17.5°	376.5
20°	327.6
22.5°	280.6
25°	239.0
27.5°	200.5
30°	166.3
32.5°	134.5
35°	106.4
37.5°	81.3
40°	61.1
42.5°	44.0
45°	32.4
47.5°	23.2
50°	17.7
52.5°	14.7
55°	12.8
57.5°	11.0
60°	9.8
62.5°	8.6
65°	7.3
67.5°	6.1
70°	4.9
72.5°	4.3
75°	3.7
77.5°	3.1
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6



TEST NUMBER: P1262315

CATALOG NUMBER: P3AS09R359727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)