

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261505

Luminaire Tested: P3AS02R359727DE010 E3CD1MB

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1261505  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R359727DE010 E3CD1MB  
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 259.0 lumens  
Efficiency: N/A  
Efficacy: 71.9 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261505  
CATALOG NUMBER: P3AS02R359727DE010 E3CD1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1261505  
 CATALOG NUMBER: P3AS02R359727DE010 E3CD1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	107	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	95	105	101	98	95	98	96	93	96	94	92	94	92	90	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	168890
5°	165441
10°	153905
15°	112850
20°	57778
25°	20832
30°	8103
35°	2838
40°	1174
45°	310
50°	273
55°	306
60°	263
65°	208
70°	256
75°	339
80°	253
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 339 cd/sqm



TEST NUMBER: P1261505  
 CATALOG NUMBER: P3AS02R359727DE010 E3CD1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.1	27.1
10°-20°	131.5	50.8
20°-30°	46.5	18.0
30°-40°	8.2	3.1
40°-50°	1.2	0.5
50°-60°	0.6	0.3
60°-70°	0.5	0.2
70°-80°	0.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	248.1	95.8
0°-40°	256.2	98.9
0°-60°	258.1	99.7
0°-90°	259.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	259.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	770	
5°	752	70
15°	497	131
25°	86	47
35°	11	8
45°	1	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1261505  
CATALOG NUMBER: P3AS02R359727DE010 E3CD1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	770.2
1°	770.0
2°	767.5
3°	762.8
4°	758.6
5°	751.6
6°	744.5
7°	736.5
8°	726.7
9°	711.4
10°	691.2
11°	663.3
12°	629.6
13°	589.7
14°	545.6
15°	497.1
17.5°	370.2
20°	247.6
22.5°	149.3
25°	86.1
27.5°	51.4
30°	32.0
32.5°	18.6
35°	10.6
37.5°	6.7
40°	4.1
42.5°	2.0
45°	1.0
47.5°	0.8
50°	0.8
52.5°	0.8
55°	0.8
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0



TEST NUMBER: P1261505  
CATALOG NUMBER: P3AS02R359727DE010 E3CD1MB

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)