

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262341

Luminaire Tested: P3AS09R409727DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262341
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409727DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 547.0 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262341
CATALOG NUMBER: P3AS09R409727DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1262341

CATALOG NUMBER: P3AS09R409727DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122797
5°	120559
10°	113647
15°	103224
20°	90681
25°	77448
30°	64162
35°	49470
40°	35209
45°	23723
50°	12929
55°	9137
60°	8596
65°	7939
70°	7052
75°	6778
80°	5430
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23723 cd/sqm



TEST NUMBER: P1262341

CATALOG NUMBER: P3AS09R409727DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.1	9.3
10°-20°	126.7	23.2
20°-30°	146.4	26.8
30°-40°	115.4	21.1
40°-50°	59.2	10.8
50°-60°	22.6	4.1
60°-70°	15.0	2.7
70°-80°	8.2	1.5
80°-90°	2.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.2	59.3
0°-40°	439.6	80.4
0°-60°	521.4	95.3
0°-90°	547.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	547.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	560	
5°	548	51
15°	455	127
25°	320	146
35°	185	115
45°	76	59
55°	24	23
65°	15	15
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1262341
CATALOG NUMBER: P3AS09R409727DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	560.0
2.5°	556.9
5°	547.7
7.5°	531.8
10°	510.4
12.5°	485.3
15°	454.7
17.5°	422.9
20°	388.6
22.5°	353.7
25°	320.1
27.5°	286.4
30°	253.4
32.5°	219.7
35°	184.8
37.5°	152.4
40°	123.0
42.5°	97.9
45°	76.5
47.5°	55.7
50°	37.9
52.5°	27.5
55°	23.9
57.5°	21.4
60°	19.6
62.5°	17.1
65°	15.3
67.5°	12.9
70°	11.0
72.5°	9.2
75°	8.0
77.5°	6.1
80°	4.3
82.5°	3.7
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)