

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261521

Luminaire Tested: P3AS02R359727DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261521
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359727DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 65.0 lumens
Efficiency: N/A
Efficacy: 18.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261521

CATALOG NUMBER: P3AS02R359727DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1261521

CATALOG NUMBER: P3AS02R359727DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20897
5°	20383
10°	18637
15°	15823
20°	12508
25°	9460
30°	6887
35°	4658
40°	2863
45°	1644
50°	989
55°	803
60°	702
65°	623
70°	513
75°	508
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1644 cd/sqm

TEST NUMBER: P1261521

CATALOG NUMBER: P3AS02R359727DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.6	13.2
10°-20°	19.2	29.6
20°-30°	17.9	27.6
30°-40°	11.0	16.9
40°-50°	4.3	6.7
50°-60°	1.9	2.9
60°-70°	1.2	1.8
70°-80°	0.6	1.0
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	45.7	70.4
0°-40°	56.7	87.3
0°-60°	62.9	96.9
0°-90°	65.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	65.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	95	
5°	93	9
15°	70	19
25°	39	18
35°	17	11
45°	5	4
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1261521

CATALOG NUMBER: P3AS02R359727DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	95.3
1°	95.4
2°	95.1
3°	94.5
4°	93.6
5°	92.6
6°	91.3
7°	89.8
8°	88.0
9°	86.0
10°	83.7
11°	81.3
12°	78.7
13°	75.9
14°	72.8
15°	69.7
17.5°	61.7
20°	53.6
22.5°	45.9
25°	39.1
27.5°	32.8
30°	27.2
32.5°	22.0
35°	17.4
37.5°	13.3
40°	10.0
42.5°	7.2
45°	5.3
47.5°	3.8
50°	2.9
52.5°	2.4
55°	2.1
57.5°	1.8
60°	1.6
62.5°	1.4
65°	1.2
67.5°	1.0
70°	0.8
72.5°	0.7
75°	0.6
77.5°	0.5
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1



TEST NUMBER: P1261521
CATALOG NUMBER: P3AS02R359727DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)