

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262346

Luminaire Tested: P3AS09R409727DE010 E3DLP1WH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1262346  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R409727DE010 E3DLP1WH  
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 714.0 lumens  
Efficiency: N/A  
Efficacy: 64.3 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262346

CATALOG NUMBER: P3AS09R409727DE010 E3DLP1WH

### Luminous Intensity Polar Plot



TEST NUMBER: P1262346

CATALOG NUMBER: P3AS09R409727DE010 E3DLP1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 98  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  |
| 3   | 104 | 99  | 94  | 91  | 102 | 97  | 93  | 90  | 95  | 91  | 88  |  | 92  | 89  | 87  |  | 90  |
| 4   | 100 | 93  | 88  | 85  | 98  | 92  | 88  | 84  | 90  | 86  | 83  |  | 88  | 85  | 82  |  | 86  |
| 5   | 96  | 88  | 83  | 79  | 94  | 88  | 83  | 79  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 83  |
| 6   | 92  | 84  | 79  | 75  | 91  | 83  | 78  | 75  | 82  | 78  | 74  |  | 81  | 77  | 74  |  | 79  |
| 7   | 88  | 80  | 75  | 71  | 87  | 79  | 74  | 71  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  |
| 8   | 85  | 76  | 71  | 68  | 84  | 76  | 71  | 67  | 75  | 70  | 67  |  | 74  | 70  | 67  |  | 73  |
| 9   | 82  | 73  | 68  | 64  | 81  | 73  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 64  |  | 70  |
| 10  | 78  | 70  | 65  | 62  | 78  | 70  | 65  | 61  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 67  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 315940 |
| 5°  | 306757 |
| 10° | 278374 |
| 15° | 229967 |
| 20° | 165891 |
| 25° | 102611 |
| 30° | 55553  |
| 35° | 28697  |
| 40° | 15601  |
| 45° | 8745   |
| 50° | 4401   |
| 55° | 3288   |
| 60° | 2938   |
| 65° | 2854   |
| 70° | 2757   |
| 75° | 2626   |
| 80° | 2273   |
| 85° | 1510   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 8745 cd/sqm

TEST NUMBER: P1262346

CATALOG NUMBER: P3AS09R409727DE010 E3DLP1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 128.5  | 18.0      |
| 10°-20°   | 275.9  | 38.6      |
| 20°-30°   | 196.9  | 27.6      |
| 30°-40°   | 72.5   | 10.1      |
| 40°-50°   | 22.8   | 3.2       |
| 50°-60°   | 7.9    | 1.1       |
| 60°-70°   | 5.4    | 0.8       |
| 70°-80°   | 3.3    | 0.5       |
| 80°-90°   | 0.9    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 601.2  | 84.2      |
| 0°-40°    | 673.6  | 94.3      |
| 0°-60°    | 704.4  | 98.7      |
| 0°-90°    | 714.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 714.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1441 |      |
| 5°  | 1394 | 128  |
| 15° | 1013 | 276  |
| 25° | 424  | 197  |
| 35° | 107  | 72   |
| 45° | 28   | 23   |
| 55° | 9    | 8    |
| 65° | 6    | 5    |
| 75° | 3    | 3    |
| 85° | 1    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1262346

CATALOG NUMBER: P3AS09R409727DE010 E3DLP1WH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1440.8 |
| 2.5°  | 1429.8 |
| 5°    | 1393.6 |
| 7.5°  | 1333.6 |
| 10°   | 1250.2 |
| 12.5° | 1144.2 |
| 15°   | 1013.0 |
| 17.5° | 866.0  |
| 20°   | 710.9  |
| 22.5° | 558.3  |
| 25°   | 424.1  |
| 27.5° | 311.3  |
| 30°   | 219.4  |
| 32.5° | 153.8  |
| 35°   | 107.2  |
| 37.5° | 76.0   |
| 40°   | 54.5   |
| 42.5° | 39.2   |
| 45°   | 28.2   |
| 47.5° | 19.0   |
| 50°   | 12.9   |
| 52.5° | 9.2    |
| 55°   | 8.6    |
| 57.5° | 8.0    |
| 60°   | 6.7    |
| 62.5° | 6.1    |
| 65°   | 5.5    |
| 67.5° | 4.9    |
| 70°   | 4.3    |
| 72.5° | 3.7    |
| 75°   | 3.1    |
| 77.5° | 2.5    |
| 80°   | 1.8    |
| 82.5° | 1.2    |
| 85°   | 0.6    |
| 87.5° | 0.6    |
| 90°   | 0.0    |

(END OF REPORT)