

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262355

Luminaire Tested: P3AS09R459727DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262355  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R459727DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 336.0 lumens  
Efficiency: N/A  
Efficacy: 30.3 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262355  
CATALOG NUMBER: P3AS09R459727DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1262355

CATALOG NUMBER: P3AS09R459727DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88	88	88	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83	83	83	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78	78	78	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74	74	74	74
6	90	82	77	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70	70	70	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66	66	66	66
8	83	74	68	65	82	73	68	65	72	68	64	71	67	64	70	67	64	62	62	62	62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59	59	59	59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57	57	57	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	126174
5°	123222
10°	113269
15°	95982
20°	74463
25°	52043
30°	32790
35°	19301
40°	10935
45°	5303
50°	1842
55°	1491
60°	1447
65°	1401
70°	1346
75°	1271
80°	1137
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5303 cd/sqm



TEST NUMBER: P1262355  
 CATALOG NUMBER: P3AS09R459727DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.8	15.4
10°-20°	116.1	34.6
20°-30°	98.6	29.3
30°-40°	47.0	14.0
40°-50°	14.2	4.2
50°-60°	3.6	1.1
60°-70°	2.7	0.8
70°-80°	1.6	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	266.5	79.3
0°-40°	313.5	93.3
0°-60°	331.3	98.6
0°-90°	336.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	336.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	575	
5°	560	52
15°	423	116
25°	215	99
35°	72	47
45°	17	14
55°	4	4
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1262355  
CATALOG NUMBER: P3AS09R459727DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	575.4
2.5°	571.8
5°	559.8
7.5°	539.1
10°	508.7
12.5°	468.5
15°	422.8
17.5°	372.0
20°	319.1
22.5°	265.3
25°	215.1
27.5°	169.5
30°	129.5
32.5°	97.4
35°	72.1
37.5°	53.2
40°	38.2
42.5°	26.4
45°	17.1
47.5°	9.6
50°	5.4
52.5°	4.2
55°	3.9
57.5°	3.6
60°	3.3
62.5°	3.0
65°	2.7
67.5°	2.4
70°	2.1
72.5°	1.8
75°	1.5
77.5°	1.2
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)