

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261552

Luminaire Tested: P3AS02R409727DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261552
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409727DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 182.0 lumens
Efficiency: N/A
Efficacy: 50.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261552

CATALOG NUMBER: P3AS02R409727DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1261552

CATALOG NUMBER: P3AS02R409727DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40852
5°	40106
10°	37808
15°	34348
20°	30173
25°	25768
30°	21345
35°	16463
40°	11708
45°	7908
50°	4298
55°	3020
60°	2851
65°	2646
70°	2372
75°	2203
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7908 cd/sqm

TEST NUMBER: P1261552

CATALOG NUMBER: P3AS02R409727DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.0	9.3
10°-20°	42.1	23.2
20°-30°	48.7	26.8
30°-40°	38.4	21.1
40°-50°	19.7	10.8
50°-60°	7.5	4.1
60°-70°	5.0	2.7
70°-80°	2.7	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	107.9	59.3
0°-40°	146.3	80.4
0°-60°	173.5	95.3
0°-90°	182.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	182.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	186	
5°	182	17
15°	151	42
25°	106	49
35°	62	38
45°	26	20
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1261552

CATALOG NUMBER: P3AS02R409727DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	186.3
2.5°	185.3
5°	182.2
7.5°	176.9
10°	169.8
12.5°	161.5
15°	151.3
17.5°	140.7
20°	129.3
22.5°	117.7
25°	106.5
27.5°	95.3
30°	84.3
32.5°	73.1
35°	61.5
37.5°	50.7
40°	40.9
42.5°	32.6
45°	25.5
47.5°	18.5
50°	12.6
52.5°	9.2
55°	7.9
57.5°	7.1
60°	6.5
62.5°	5.7
65°	5.1
67.5°	4.3
70°	3.7
72.5°	3.1
75°	2.6
77.5°	2.0
80°	1.4
82.5°	1.2
85°	0.6
87.5°	0.4
90°	0.0

(END OF REPORT)