

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262356

Luminaire Tested: P3AS09R459727DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262356
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459727DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 685.0 lumens
Efficiency: N/A
Efficacy: 61.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262356
CATALOG NUMBER: P3AS09R459727DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1262356
 CATALOG NUMBER: P3AS09R459727DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83			83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74			74
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70			70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62			62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59			59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	257238
5°	251221
10°	230924
15°	195665
20°	151820
25°	106119
30°	66846
35°	39351
40°	22270
45°	10823
50°	3753
55°	3058
60°	2938
65°	2854
70°	2757
75°	2626
80°	2273
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10823 cd/sqm



TEST NUMBER: P1262356
 CATALOG NUMBER: P3AS09R459727DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.6	15.4
10°-20°	236.7	34.6
20°-30°	201.0	29.3
30°-40°	95.9	14.0
40°-50°	28.9	4.2
50°-60°	7.3	1.1
60°-70°	5.4	0.8
70°-80°	3.3	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	543.3	79.3
0°-40°	639.2	93.3
0°-60°	675.4	98.6
0°-90°	685.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	685.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1173	
5°	1141	106
15°	862	237
25°	439	201
35°	147	96
45°	35	29
55°	8	7
65°	6	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1262356
CATALOG NUMBER: P3AS09R459727DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1173.1
2.5°	1165.8
5°	1141.3
7.5°	1099.0
10°	1037.1
12.5°	955.0
15°	861.9
17.5°	758.4
20°	650.6
22.5°	540.9
25°	438.6
27.5°	345.5
30°	264.0
32.5°	198.5
35°	147.0
37.5°	108.4
40°	77.8
42.5°	53.9
45°	34.9
47.5°	19.6
50°	11.0
52.5°	8.6
55°	8.0
57.5°	7.4
60°	6.7
62.5°	6.1
65°	5.5
67.5°	4.9
70°	4.3
72.5°	3.7
75°	3.1
77.5°	2.5
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)