

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261571

Luminaire Tested: P3AS02R459727DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459727DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 227.9 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261571

CATALOG NUMBER: P3AS02R459727DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1261571

CATALOG NUMBER: P3AS02R459727DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85629
5°	83623
10°	76863
15°	65131
20°	50521
25°	35325
30°	22257
35°	13090
40°	7414
45°	3597
50°	1262
55°	1032
60°	965
65°	934
70°	898
75°	847
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3597 cd/sqm

TEST NUMBER: P1261571

CATALOG NUMBER: P3AS02R459727DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.2	15.4
10°-20°	78.8	34.6
20°-30°	66.9	29.3
30°-40°	31.9	14.0
40°-50°	9.6	4.2
50°-60°	2.4	1.1
60°-70°	1.8	0.8
70°-80°	1.1	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	180.8	79.3
0°-40°	212.8	93.3
0°-60°	224.8	98.6
0°-90°	227.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	227.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	390	
5°	380	35
15°	287	79
25°	146	67
35°	49	32
45°	12	10
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1261571

CATALOG NUMBER: P3AS02R459727DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	390.5
2.5°	388.0
5°	379.9
7.5°	365.8
10°	345.2
12.5°	317.9
15°	286.9
17.5°	252.4
20°	216.5
22.5°	180.0
25°	146.0
27.5°	115.0
30°	87.9
32.5°	66.1
35°	48.9
37.5°	36.1
40°	25.9
42.5°	17.9
45°	11.6
47.5°	6.5
50°	3.7
52.5°	2.9
55°	2.7
57.5°	2.4
60°	2.2
62.5°	2.0
65°	1.8
67.5°	1.6
70°	1.4
72.5°	1.2
75°	1.0
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)