

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262359

Luminaire Tested: P3AS09R459727DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262359
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459727DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 442.0 lumens
Efficiency: N/A
Efficacy: 39.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262359

CATALOG NUMBER: P3AS09R459727DE010 E3DL1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1262359

CATALOG NUMBER: P3AS09R459727DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86		
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74		
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69		
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64		
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56		
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53		
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131656
5°	128659
10°	118680
15°	103202
20°	84777
25°	65955
30°	48716
35°	34265
40°	21383
45°	11598
50°	6277
55°	5390
60°	4824
65°	4151
70°	3526
75°	3643
80°	3157
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 11598 cd/sqm

TEST NUMBER: P1262359

CATALOG NUMBER: P3AS09R459727DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	12.2
10°-20°	125.7	28.4
20°-30°	124.8	28.2
30°-40°	80.3	18.2
40°-50°	30.9	7.0
50°-60°	12.6	2.8
60°-70°	7.9	1.8
70°-80°	4.3	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	304.6	68.9
0°-40°	384.9	87.1
0°-60°	428.4	96.9
0°-90°	442.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	442.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	600	
5°	584	54
15°	455	126
25°	273	125
35°	128	80
45°	37	31
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1262359

CATALOG NUMBER: P3AS09R459727DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	600.4
2.5°	597.3
5°	584.5
7.5°	562.4
10°	533.0
12.5°	496.2
15°	454.6
17.5°	409.2
20°	363.3
22.5°	316.7
25°	272.6
27.5°	231.0
30°	192.4
32.5°	158.7
35°	128.0
37.5°	100.5
40°	74.7
42.5°	53.9
45°	37.4
47.5°	25.1
50°	18.4
52.5°	15.3
55°	14.1
57.5°	12.3
60°	11.0
62.5°	9.2
65°	8.0
67.5°	6.7
70°	5.5
72.5°	4.9
75°	4.3
77.5°	3.1
80°	2.5
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)