

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262365

Luminaire Tested: P3AS09R459727DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262365
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459727DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 532.0 lumens
Efficiency: N/A
Efficacy: 47.9 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262365
CATALOG NUMBER: P3AS09R459727DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1262365
 CATALOG NUMBER: P3AS09R459727DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112798
5°	110808
10°	104852
15°	95619
20°	84544
25°	73432
30°	63022
35°	52521
40°	39130
45°	23971
50°	11087
55°	8678
60°	8333
65°	7627
70°	7052
75°	6778
80°	6188
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23971 cd/sqm



TEST NUMBER: P1262365
 CATALOG NUMBER: P3AS09R459727DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	8.8
10°-20°	117.3	22.0
20°-30°	139.3	26.2
30°-40°	121.1	22.8
40°-50°	60.7	11.4
50°-60°	21.1	4.0
60°-70°	14.8	2.8
70°-80°	8.2	1.5
80°-90°	2.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	303.6	57.1
0°-40°	424.7	79.8
0°-60°	506.5	95.2
0°-90°	532.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	532.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	514	
5°	503	47
15°	421	117
25°	304	139
35°	196	121
45°	77	61
55°	23	21
65°	15	15
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1262365
CATALOG NUMBER: P3AS09R459727DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	514.4
2.5°	511.9
5°	503.4
7.5°	489.9
10°	470.9
12.5°	447.6
15°	421.2
17.5°	391.8
20°	362.3
22.5°	332.3
25°	303.5
27.5°	275.9
30°	248.9
32.5°	223.2
35°	196.2
37.5°	167.4
40°	136.7
42.5°	106.7
45°	77.3
47.5°	50.9
50°	32.5
52.5°	25.1
55°	22.7
57.5°	20.8
60°	19.0
62.5°	17.2
65°	14.7
67.5°	12.9
70°	11.0
72.5°	9.2
75°	8.0
77.5°	6.1
80°	4.9
82.5°	3.7
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)