

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261575

Luminaire Tested: P3AS02R459727DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1261575  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R459727DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 177.0 lumens  
Efficiency: N/A  
Efficacy: 49.2 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1261575  
CATALOG NUMBER: P3AS02R459727DE010 E3DLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1261575  
 CATALOG NUMBER: P3AS02R459727DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	37519
5°	36870
10°	34891
15°	31805
20°	28142
25°	24437
30°	20965
35°	17480
40°	13024
45°	7970
50°	3684
55°	2867
60°	2763
65°	2542
70°	2372
75°	2288
80°	2020
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7970 cd/sqm



TEST NUMBER: P1261575  
 CATALOG NUMBER: P3AS02R459727DE010 E3DLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	15.6	8.8
10°-20°	39.0	22.0
20°-30°	46.4	26.2
30°-40°	40.3	22.8
40°-50°	20.2	11.4
50°-60°	7.0	4.0
60°-70°	4.9	2.8
70°-80°	2.8	1.6
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	101.0	57.1
0°-40°	141.3	79.8
0°-60°	168.5	95.2
0°-90°	177.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	177.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	171	
5°	168	16
15°	140	39
25°	101	46
35°	65	40
45°	26	20
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1261575  
CATALOG NUMBER: P3AS02R459727DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	171.1
2.5°	170.3
5°	167.5
7.5°	163.0
10°	156.7
12.5°	148.9
15°	140.1
17.5°	130.3
20°	120.6
22.5°	110.6
25°	101.0
27.5°	91.8
30°	82.8
32.5°	74.2
35°	65.3
37.5°	55.7
40°	45.5
42.5°	35.5
45°	25.7
47.5°	16.9
50°	10.8
52.5°	8.4
55°	7.5
57.5°	6.9
60°	6.3
62.5°	5.7
65°	4.9
67.5°	4.3
70°	3.7
72.5°	3.1
75°	2.7
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.6
87.5°	0.4
90°	0.0

(END OF REPORT)