

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262379

Luminaire Tested: P3AS09R509727DE010 E3D1H

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262379  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R509727DE010 E3D1H  
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 851.0 lumens  
Efficiency: N/A  
Efficacy: 76.7 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262379  
CATALOG NUMBER: P3AS09R509727DE010 E3D1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1262379

CATALOG NUMBER: P3AS09R509727DE010 E3D1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	297388
5°	289478
10°	276236
15°	250081
20°	216365
25°	177470
30°	101940
35°	31668
40°	8502
45°	2977
50°	716
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2977 cd/sqm



TEST NUMBER: P1262379  
 CATALOG NUMBER: P3AS09R509727DE010 E3D1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.2	14.5
10°-20°	305.2	35.9
20°-30°	320.8	37.7
30°-40°	91.8	10.8
40°-50°	9.0	1.1
50°-60°	0.7	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	749.2	88.0
0°-40°	841.0	98.8
0°-60°	850.7	100.0
0°-90°	851.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	851.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1356	
5°	1315	123
15°	1102	305
25°	734	321
35°	118	92
45°	10	9
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1262379  
CATALOG NUMBER: P3AS09R509727DE010 E3D1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1356.2
1°	1354.1
2°	1348.1
3°	1339.4
4°	1327.7
5°	1315.1
6°	1301.6
7°	1287.2
8°	1273.6
9°	1258.0
10°	1240.6
11°	1220.5
12°	1197.4
13°	1168.6
14°	1137.3
15°	1101.6
16°	1063.8
17°	1027.1
18°	989.6
19°	956.6
20°	927.2
21°	898.9
22°	866.8
23°	829.9
24°	786.6
25°	733.5
26°	675.9
27°	611.6
28°	547.6
29°	478.6
30°	402.6
31°	331.5
32°	266.0
32.5°	237.5
33°	208.7
34°	160.0
35°	118.3
36°	86.8
37°	64.6
37.5°	55.8
38°	48.3
39°	37.5
40°	29.7
42.5°	16.8
45°	9.6



TEST NUMBER: P1262379  
CATALOG NUMBER: P3AS09R509727DE010 E3D1H

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	5.4
50°	2.1
52.5°	0.9
55°	0.6
57.5°	0.6
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)