

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261606

Luminaire Tested: P3AS02R509727DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261606
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509727DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 179.0 lumens
Efficiency: N/A
Efficacy: 49.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261606

CATALOG NUMBER: P3AS02R509727DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1261606

CATALOG NUMBER: P3AS02R509727DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36379
5°	35835
10°	34246
15°	31714
20°	28516
25°	25066
30°	21320
35°	17293
40°	12996
45°	8373
50°	3957
55°	3135
60°	2938
65°	2750
70°	2500
75°	2288
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8373 cd/sqm

TEST NUMBER: P1261606

CATALOG NUMBER: P3AS02R509727DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.3	8.5
10°-20°	39.0	21.8
20°-30°	47.3	26.4
30°-40°	40.2	22.4
40°-50°	20.9	11.7
50°-60°	7.5	4.2
60°-70°	5.2	2.9
70°-80°	2.8	1.6
80°-90°	0.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	101.6	56.7
0°-40°	141.7	79.2
0°-60°	170.1	95.0
0°-90°	179.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	179.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	166	
5°	163	15
15°	140	39
25°	104	47
35°	65	40
45°	27	21
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1261606

CATALOG NUMBER: P3AS02R509727DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	165.9
2.5°	165.3
5°	162.8
7.5°	159.1
10°	153.8
12.5°	147.1
15°	139.7
17.5°	131.4
20°	122.2
22.5°	112.8
25°	103.6
27.5°	94.0
30°	84.2
32.5°	74.4
35°	64.6
37.5°	55.0
40°	45.4
42.5°	36.2
45°	27.0
47.5°	18.0
50°	11.6
52.5°	9.0
55°	8.2
57.5°	7.4
60°	6.7
62.5°	5.9
65°	5.3
67.5°	4.5
70°	3.9
72.5°	3.3
75°	2.7
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)