

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262384

Luminaire Tested: P3AS09R509727DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509727DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 338.0 lumens
Efficiency: N/A
Efficacy: 30.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262384

CATALOG NUMBER: P3AS09R509727DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1262384

CATALOG NUMBER: P3AS09R509727DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107623
5°	105437
10°	98773
15°	88423
20°	74416
25°	56786
30°	36917
35°	21870
40°	12652
45°	6326
50°	2354
55°	1835
60°	1710
65°	1557
70°	1539
75°	1525
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6326 cd/sqm

TEST NUMBER: P1262384

CATALOG NUMBER: P3AS09R509727DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	13.2
10°-20°	107.7	31.9
20°-30°	105.7	31.3
30°-40°	53.2	15.8
40°-50°	16.8	5.0
50°-60°	4.4	1.3
60°-70°	3.1	0.9
70°-80°	1.9	0.6
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	257.9	76.3
0°-40°	311.2	92.1
0°-60°	332.3	98.3
0°-90°	338.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	338.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	491	
5°	479	45
15°	390	108
25°	235	106
35°	82	53
45°	20	17
55°	5	4
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1262384

CATALOG NUMBER: P3AS09R509727DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	490.8
2.5°	487.7
5°	479.0
7.5°	463.4
10°	443.6
12.5°	418.0
15°	389.5
17.5°	356.4
20°	318.9
22.5°	278.3
25°	234.7
27.5°	188.4
30°	145.8
32.5°	109.7
35°	81.7
37.5°	60.4
40°	44.2
42.5°	31.3
45°	20.4
47.5°	11.7
50°	6.9
52.5°	5.1
55°	4.8
57.5°	4.2
60°	3.9
62.5°	3.6
65°	3.0
67.5°	2.7
70°	2.4
72.5°	2.1
75°	1.8
77.5°	1.5
80°	1.2
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)