

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262390

Luminaire Tested: P3AS09R509727DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262390
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509727DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 263.0 lumens
Efficiency: N/A
Efficacy: 23.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262390
CATALOG NUMBER: P3AS09R509727DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1262390
 CATALOG NUMBER: P3AS09R509727DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53439
5°	52652
10°	50322
15°	46606
20°	41887
25°	36825
30°	31321
35°	25404
40°	19064
45°	12280
50°	5833
55°	4588
60°	4342
65°	4047
70°	3654
75°	3304
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12280 cd/sqm



TEST NUMBER: P1262390
 CATALOG NUMBER: P3AS09R509727DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.4	8.5
10°-20°	57.2	21.8
20°-30°	69.6	26.4
30°-40°	59.0	22.4
40°-50°	30.6	11.6
50°-60°	11.0	4.2
60°-70°	7.6	2.9
70°-80°	4.2	1.6
80°-90°	1.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	149.2	56.7
0°-40°	208.2	79.2
0°-60°	249.9	95.0
0°-90°	263.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	263.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	244	
5°	239	22
15°	205	57
25°	152	70
35°	95	59
45°	40	31
55°	12	11
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1262390
CATALOG NUMBER: P3AS09R509727DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	243.7
2.5°	242.8
5°	239.2
7.5°	233.8
10°	226.0
12.5°	216.1
15°	205.3
17.5°	193.0
20°	179.5
22.5°	165.7
25°	152.2
27.5°	138.1
30°	123.7
32.5°	109.3
35°	94.9
37.5°	80.7
40°	66.6
42.5°	53.1
45°	39.6
47.5°	26.4
50°	17.1
52.5°	13.2
55°	12.0
57.5°	10.8
60°	9.9
62.5°	8.7
65°	7.8
67.5°	6.6
70°	5.7
72.5°	4.8
75°	3.9
77.5°	3.0
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)