

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261609

Luminaire Tested: P3AS02R509727DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509727DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 151.0 lumens
Efficiency: N/A
Efficacy: 41.9 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261609
CATALOG NUMBER: P3AS02R509727DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1261609
 CATALOG NUMBER: P3AS02R509727DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73			
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68			
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60			
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56			
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43922
5°	42747
10°	39411
15°	34665
20°	29006
25°	22985
30°	16863
35°	11591
40°	7385
45°	4124
50°	2217
55°	1873
60°	1623
65°	1505
70°	1282
75°	1186
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4124 cd/sqm



TEST NUMBER: P1261609
 CATALOG NUMBER: P3AS02R509727DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.0	11.9
10°-20°	42.3	28.0
20°-30°	43.2	28.6
30°-40°	27.4	18.2
40°-50°	10.9	7.2
50°-60°	4.4	2.9
60°-70°	2.9	1.9
70°-80°	1.4	0.9
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	103.5	68.6
0°-40°	130.9	86.7
0°-60°	146.3	96.9
0°-90°	151.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	151.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	200	
5°	194	18
15°	153	42
25°	95	43
35°	43	27
45°	13	11
55°	5	4
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1261609
CATALOG NUMBER: P3AS02R509727DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	200.3
2.5°	198.9
5°	194.2
7.5°	186.8
10°	177.0
12.5°	165.3
15°	152.7
17.5°	138.8
20°	124.3
22.5°	109.7
25°	95.0
27.5°	80.3
30°	66.6
32.5°	54.4
35°	43.3
37.5°	33.9
40°	25.8
42.5°	19.0
45°	13.3
47.5°	9.0
50°	6.5
52.5°	5.5
55°	4.9
57.5°	4.3
60°	3.7
62.5°	3.3
65°	2.9
67.5°	2.5
70°	2.0
72.5°	1.6
75°	1.4
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)