

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262392

Luminaire Tested: P3AS09R509727DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509727DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 537.0 lumens
Efficiency: N/A
Efficacy: 48.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262392

CATALOG NUMBER: P3AS09R509727DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1262392

CATALOG NUMBER: P3AS09R509727DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109136
5°	107528
10°	102759
15°	95165
20°	85524
25°	75174
30°	63934
35°	51852
40°	38959
45°	25088
50°	11906
55°	9366
60°	8859
65°	8250
70°	7437
75°	6778
80°	6188
85°	6290

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25088 cd/sqm

TEST NUMBER: P1262392

CATALOG NUMBER: P3AS09R509727DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	8.5
10°-20°	116.9	21.8
20°-30°	142.0	26.4
30°-40°	120.4	22.4
40°-50°	62.6	11.6
50°-60°	22.6	4.2
60°-70°	15.6	2.9
70°-80°	8.5	1.6
80°-90°	2.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	304.7	56.7
0°-40°	425.1	79.2
0°-60°	510.2	95.0
0°-90°	537.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	537.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	498	
5°	488	46
15°	419	117
25°	311	142
35°	194	120
45°	81	63
55°	24	23
65°	16	16
75°	8	8
85°	2	3
90°	0	

TEST NUMBER: P1262392

CATALOG NUMBER: P3AS09R509727DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	497.7
2.5°	495.8
5°	488.5
7.5°	477.4
10°	461.5
12.5°	441.3
15°	419.2
17.5°	394.1
20°	366.5
22.5°	338.3
25°	310.7
27.5°	281.9
30°	252.5
32.5°	223.1
35°	193.7
37.5°	164.9
40°	136.1
42.5°	108.5
45°	80.9
47.5°	53.9
50°	34.9
52.5°	27.0
55°	24.5
57.5°	22.1
60°	20.2
62.5°	17.8
65°	15.9
67.5°	13.5
70°	11.6
72.5°	9.8
75°	8.0
77.5°	6.1
80°	4.9
82.5°	3.7
85°	2.5
87.5°	1.2
90°	0.0

(END OF REPORT)