

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262469

Luminaire Tested: P3AS09R659727DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659727DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 97CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 731.0 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262469
CATALOG NUMBER: P3AS09R659727DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1262469
 CATALOG NUMBER: P3AS09R659727DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82				82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77				77
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67				67
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63				63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59				59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52				52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195883
5°	181884
10°	175882
15°	169490
20°	156697
25°	142774
30°	110321
35°	63952
40°	25362
45°	10823
50°	2559
55°	344
60°	263
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10823 cd/sqm



TEST NUMBER: P1262469
 CATALOG NUMBER: P3AS09R659727DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.9	10.7
10°-20°	208.0	28.5
20°-30°	263.3	36.0
30°-40°	149.9	20.5
40°-50°	29.8	4.1
50°-60°	1.5	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	549.3	75.1
0°-40°	699.2	95.7
0°-60°	730.6	99.9
0°-90°	731.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	731.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	893	
5°	826	78
15°	747	208
25°	590	263
35°	239	150
45°	35	30
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1262469
CATALOG NUMBER: P3AS09R659727DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	893.3
1°	886.7
2°	872.2
3°	855.4
4°	838.9
5°	826.3
6°	817.0
7°	809.4
8°	802.8
9°	796.2
10°	789.9
11°	783.0
12°	775.8
13°	767.1
14°	757.8
15°	746.6
16°	733.4
17°	719.0
18°	703.4
19°	686.9
20°	671.5
21°	655.9
22°	641.8
23°	627.1
24°	609.9
25°	590.1
26°	566.4
27°	537.8
28°	505.7
29°	471.4
30°	435.7
31°	396.3
32°	357.2
32.5°	337.1
33°	317.6
34°	277.9
35°	238.9
36°	202.8
37°	167.1
37.5°	148.7
38°	134.0
39°	108.5
40°	88.6
42.5°	54.7
45°	34.9



TEST NUMBER: P1262469
CATALOG NUMBER: P3AS09R659727DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	20.4
50°	7.5
52.5°	1.5
55°	0.9
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)