

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262481

Luminaire Tested: P3AS09R659727DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262481
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659727DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 483.0 lumens
Efficiency: N/A
Efficacy: 43.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262481
CATALOG NUMBER: P3AS09R659727DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1262481
 CATALOG NUMBER: P3AS09R659727DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 102 | 100 | 98 | 99 | 97 | 95 | 95 | 94 | 93 | 91 | | | | 91 |
| 2 | 105 | 99 | 94 | 90 | 103 | 97 | 93 | 89 | 94 | 90 | 87 | 91 | 88 | 85 | 88 | 86 | 84 | 82 | | | | 82 |
| 3 | 99 | 91 | 85 | 80 | 96 | 89 | 84 | 79 | 87 | 82 | 78 | 84 | 80 | 77 | 82 | 78 | 76 | 74 | | | | 74 |
| 4 | 92 | 83 | 77 | 72 | 90 | 82 | 76 | 71 | 80 | 75 | 70 | 78 | 73 | 70 | 76 | 72 | 69 | 67 | | | | 67 |
| 5 | 87 | 77 | 70 | 65 | 85 | 76 | 69 | 65 | 74 | 68 | 64 | 72 | 67 | 63 | 71 | 66 | 63 | 61 | | | | 61 |
| 6 | 82 | 71 | 64 | 59 | 80 | 70 | 64 | 59 | 69 | 63 | 58 | 67 | 62 | 58 | 66 | 61 | 58 | 56 | | | | 56 |
| 7 | 77 | 66 | 59 | 54 | 75 | 65 | 59 | 54 | 64 | 58 | 54 | 63 | 57 | 53 | 61 | 57 | 53 | 51 | | | | 51 |
| 8 | 72 | 61 | 55 | 50 | 71 | 61 | 54 | 50 | 60 | 54 | 49 | 59 | 53 | 49 | 58 | 53 | 49 | 47 | | | | 47 |
| 9 | 68 | 57 | 51 | 46 | 67 | 57 | 50 | 46 | 56 | 50 | 46 | 55 | 49 | 46 | 54 | 49 | 45 | 44 | | | | 44 |
| 10 | 65 | 54 | 47 | 43 | 64 | 53 | 47 | 43 | 52 | 47 | 43 | 52 | 46 | 42 | 51 | 46 | 42 | 41 | | | | 41 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 85958 |
| 5° | 84790 |
| 10° | 81940 |
| 15° | 77276 |
| 20° | 71290 |
| 25° | 64697 |
| 30° | 57325 |
| 35° | 48774 |
| 40° | 38816 |
| 45° | 27383 |
| 50° | 15897 |
| 55° | 8678 |
| 60° | 8070 |
| 65° | 7316 |
| 70° | 6668 |
| 75° | 6270 |
| 80° | 5430 |
| 85° | 4529 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27383 cd/sqm



TEST NUMBER: P1262481
 CATALOG NUMBER: P3AS09R659727DE010 E3DLD1WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 36.2 | 7.5 |
| 10°-20° | 95.2 | 19.7 |
| 20°-30° | 122.4 | 25.3 |
| 30°-40° | 113.2 | 23.4 |
| 40°-50° | 68.4 | 14.2 |
| 50°-60° | 23.3 | 4.8 |
| 60°-70° | 14.0 | 2.9 |
| 70°-80° | 7.9 | 1.6 |
| 80°-90° | 2.2 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 253.9 | 52.6 |
| 0°-40° | 367.1 | 76.0 |
| 0°-60° | 458.8 | 95.0 |
| 0°-90° | 483.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 483.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 392 | |
| 5° | 385 | 36 |
| 15° | 340 | 95 |
| 25° | 267 | 122 |
| 35° | 182 | 113 |
| 45° | 88 | 68 |
| 55° | 23 | 23 |
| 65° | 14 | 14 |
| 75° | 7 | 8 |
| 85° | 2 | 2 |
| 90° | 0 | |

TEST NUMBER: P1262481

CATALOG NUMBER: P3AS09R659727DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 392.0 |
| 2.5° | 390.1 |
| 5° | 385.2 |
| 7.5° | 377.9 |
| 10° | 368.0 |
| 12.5° | 355.8 |
| 15° | 340.4 |
| 17.5° | 323.9 |
| 20° | 305.5 |
| 22.5° | 286.5 |
| 25° | 267.4 |
| 27.5° | 247.2 |
| 30° | 226.4 |
| 32.5° | 205.5 |
| 35° | 182.2 |
| 37.5° | 159.5 |
| 40° | 135.6 |
| 42.5° | 111.6 |
| 45° | 88.3 |
| 47.5° | 66.9 |
| 50° | 46.6 |
| 52.5° | 29.4 |
| 55° | 22.7 |
| 57.5° | 20.2 |
| 60° | 18.4 |
| 62.5° | 15.9 |
| 65° | 14.1 |
| 67.5° | 12.3 |
| 70° | 10.4 |
| 72.5° | 9.2 |
| 75° | 7.4 |
| 77.5° | 6.1 |
| 80° | 4.3 |
| 82.5° | 3.1 |
| 85° | 1.8 |
| 87.5° | 1.2 |
| 90° | 0.0 |

(END OF REPORT)