

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1261748

Luminaire Tested: P3AS05R109727DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1261748
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R109727DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R10 optic, 2700K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 285.0 lumens
Efficiency: N/A
Efficacy: 36.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1261748

CATALOG NUMBER: P3AS05R109727DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1261748

CATALOG NUMBER: P3AS05R109727DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71880
5°	69932
10°	63904
15°	55982
20°	48024
25°	40091
30°	32081
35°	24066
40°	17461
45°	11412
50°	7130
55°	4817
60°	4254
65°	3943
70°	3719
75°	3389
80°	3157
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11412 cd/sqm

TEST NUMBER: P1261748

CATALOG NUMBER: P3AS05R109727DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.3	10.3
10°-20°	68.7	24.1
20°-30°	75.7	26.6
30°-40°	56.7	19.9
40°-50°	29.4	10.3
50°-60°	12.2	4.3
60°-70°	7.6	2.7
70°-80°	4.2	1.5
80°-90°	1.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.7	61.0
0°-40°	230.4	80.9
0°-60°	271.9	95.4
0°-90°	285.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	285.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	328	
5°	318	29
15°	247	69
25°	166	76
35°	90	57
45°	37	29
55°	13	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1261748

CATALOG NUMBER: P3AS05R109727DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	327.8
1°	328.2
2°	327.1
3°	324.9
4°	321.7
5°	317.7
6°	312.7
7°	307.3
8°	300.8
9°	293.9
10°	287.0
12.5°	267.2
15°	246.6
17.5°	226.0
20°	205.8
22.5°	185.2
25°	165.7
27.5°	146.2
30°	126.7
32.5°	107.6
35°	89.9
37.5°	74.7
40°	61.0
42.5°	48.4
45°	36.8
47.5°	27.8
50°	20.9
52.5°	15.5
55°	12.6
57.5°	11.2
60°	9.7
62.5°	8.7
65°	7.6
67.5°	6.5
70°	5.8
72.5°	4.7
75°	4.0
77.5°	3.2
80°	2.5
82.5°	1.8
85°	1.1
87.5°	0.4
90°	0.0

(END OF REPORT)