

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262493

Luminaire Tested: P3AS09R709727DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262493
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709727DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 765.9 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262493

CATALOG NUMBER: P3AS09R709727DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1262493

CATALOG NUMBER: P3AS09R709727DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152115
5°	145146
10°	138096
15°	134394
20°	129441
25°	122499
30°	113942
35°	95700
40°	61687
45°	28654
50°	7505
55°	1873
60°	1886
65°	1608
70°	1539
75°	1525
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28654 cd/sqm

TEST NUMBER: P1262493

CATALOG NUMBER: P3AS09R709727DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.7	8.1
10°-20°	166.4	21.7
20°-30°	232.4	30.3
30°-40°	215.5	28.1
40°-50°	77.2	10.1
50°-60°	6.5	0.9
60°-70°	3.3	0.4
70°-80°	2.1	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	460.5	60.1
0°-40°	676.0	88.3
0°-60°	759.8	99.2
0°-90°	765.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	765.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	694	
5°	659	62
15°	592	166
25°	506	232
35°	358	215
45°	92	77
55°	5	7
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1262493

CATALOG NUMBER: P3AS09R709727DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	693.7
2.5°	683.3
5°	659.4
7.5°	637.3
10°	620.2
12.5°	606.1
15°	592.0
17.5°	574.9
20°	554.7
22.5°	531.4
25°	506.3
27.5°	480.6
30°	450.0
32.5°	410.8
35°	357.5
37.5°	289.6
40°	215.5
42.5°	146.9
45°	92.4
47.5°	51.4
50°	22.0
52.5°	7.3
55°	4.9
57.5°	4.3
60°	4.3
62.5°	3.7
65°	3.1
67.5°	3.1
70°	2.4
72.5°	2.4
75°	1.8
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)