

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262500

Luminaire Tested: P3AS09R709727DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709727DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 302.0 lumens
Efficiency: N/A
Efficacy: 27.2 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262500

CATALOG NUMBER: P3AS09R709727DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1262500

CATALOG NUMBER: P3AS09R709727DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58460
5°	57759
10°	56089
15°	53712
20°	50311
25°	45704
30°	39500
35°	31481
40°	22929
45°	15071
50°	7062
55°	2179
60°	2105
65°	2024
70°	1923
75°	2033
80°	1894
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15071 cd/sqm

TEST NUMBER: P1262500

CATALOG NUMBER: P3AS09R709727DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.7	8.2
10°-20°	66.2	21.9
20°-30°	86.1	28.5
30°-40°	73.1	24.2
40°-50°	37.7	12.5
50°-60°	7.3	2.4
60°-70°	3.9	1.3
70°-80°	2.4	0.8
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	177.0	58.6
0°-40°	250.0	82.8
0°-60°	295.0	97.7
0°-90°	302.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	302.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	267	
5°	262	25
15°	237	66
25°	189	86
35°	118	73
45°	49	38
55°	6	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1262500

CATALOG NUMBER: P3AS09R709727DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	266.6
2.5°	265.7
5°	262.4
7.5°	257.6
10°	251.9
12.5°	244.7
15°	236.6
17.5°	226.7
20°	215.6
22.5°	203.0
25°	188.9
27.5°	173.0
30°	156.0
32.5°	137.1
35°	117.6
37.5°	98.4
40°	80.1
42.5°	63.0
45°	48.6
47.5°	35.7
50°	20.7
52.5°	9.0
55°	5.7
57.5°	5.4
60°	4.8
62.5°	4.5
65°	3.9
67.5°	3.6
70°	3.0
72.5°	2.7
75°	2.4
77.5°	1.8
80°	1.5
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)