

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262506

Luminaire Tested: P3AS09R709727DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262506
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709727DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 216.0 lumens
Efficiency: N/A
Efficacy: 19.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262506

CATALOG NUMBER: P3AS09R709727DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1262506

CATALOG NUMBER: P3AS09R709727DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50676
5°	49725
10°	46893
15°	42566
20°	37220
25°	31405
30°	25725
35°	19943
40°	14284
45°	9024
50°	4503
55°	2753
60°	2368
65°	2179
70°	1923
75°	1779
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9024 cd/sqm

TEST NUMBER: P1262506

CATALOG NUMBER: P3AS09R709727DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.1	9.8
10°-20°	52.2	24.2
20°-30°	59.4	27.5
30°-40°	46.5	21.5
40°-50°	22.8	10.6
50°-60°	7.0	3.2
60°-70°	4.2	1.9
70°-80°	2.2	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	132.7	61.4
0°-40°	179.1	82.9
0°-60°	208.9	96.7
0°-90°	216.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	216.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	231	
5°	226	21
15°	188	52
25°	130	59
35°	74	46
45°	29	23
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1262506

CATALOG NUMBER: P3AS09R709727DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	231.1
2.5°	229.8
5°	225.9
7.5°	219.6
10°	210.6
12.5°	200.1
15°	187.5
17.5°	174.0
20°	159.5
22.5°	144.5
25°	129.8
27.5°	115.4
30°	101.6
32.5°	87.7
35°	74.5
37.5°	61.9
40°	49.9
42.5°	38.8
45°	29.1
47.5°	20.4
50°	13.2
52.5°	8.7
55°	7.2
57.5°	6.3
60°	5.4
62.5°	4.8
65°	4.2
67.5°	3.6
70°	3.0
72.5°	2.4
75°	2.1
77.5°	1.8
80°	1.2
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)